

PICCOLO ABS B 65 G



Sample photo

Order symbol: ABS B 65 G
Product nbr: 8784303
Description: Enclosure, ABS
Remarks: Grey cover

EAN: 6418074001993
EI. number:
 Finland: 3423451
 Electric No. Denmark: 8212001802
 Electric No. Italy: 7211010
 Electric No. Sweden: 2536701

Including: Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

Dimensions:	Length	Width	Height	Accessories:	
mm:	110	80	65	B-3	DIN-35 Mounting rail
inch:	4.3	3.1	2.6	FP 22040	Wall fastening lug (2 pcs)

Materials:		Rating:	
Material:	ABS	Ingress Protection (EN 60529): IP66/IP67	
Base colour:	RAL 7035 -light grey	Impact Resistance (EN 62262): IK07	
Cover screws material:	Polyamide	Electrical insulation: Totally insulated	
Cover colour:	RAL 7035 -light grey	Halogen free (DIN/VDE 0472, Part 815): 1	
Cover screws colour:	Grey	Flammability Rating: UL 94 HB	
Gasket material:	Polyurethane	Glow Wire Test (IEC 695-2-1) °C: 650	
		NEMA Class: NEMA 1, 4X, 6, 12, 13	

Temperatures:	
Temperature °C (short term):	-40 ... 80 °C
Temperature °C (continuous):	-40 ... 60 °C
Temperature °F (short term):	-40 ... 175 °F
Temperature °F (continuous):	-40 ... 140 °F

Accessories:	
B-MP	Mounting plate

