

**PICCOLO ABS C 65 G**



Sample photo

**Order symbol:** ABS C 65 G  
**Product nbr:** 8784305  
**Description:** Enclosure, ABS  
**Remarks:** Grey cover

**EAN:** 6418074002075  
**El. number:**  
 Finland: 3423455  
 Electric No. 8212001844  
 Denmark:  
 Electric No. Italy: 7211020  
 Electric No. Sweden: 2536707

Including: Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

Dimensions:	Length	Width	Height	Accessories:	
mm:	140	80	65	CHM-3	DIN-35 Mounting rail
inch:	5.5	3.1	2.6	FP 22040	Wall fastening lug (2 pcs)

Materials:	Material:	Rating:
<b>Material:</b>	ABS	Ingress Protection (EN 60529): IP66/IP67
<b>Base colour:</b>	RAL 7035 -light grey	Impact Resistance (EN 62262): IK07
<b>Cover screws material:</b>	Polyamide	Electrical insulation: Totally insulated
<b>Cover colour:</b>	RAL 7035 -light grey	Halogen free (DIN/VDE 0472, Part 815): 1
<b>Cover screws colour:</b>	Grey	Flammability Rating: UL 94 HB
<b>Gasket material:</b>	Polyurethane	Glow Wire Test (IEC 695-2-1) °C: 650
		NEMA Class: NEMA 1, 4X, 6, 12, 13

**Temperatures:**

Temperature °C (short term):	-40 ... 80 °C
Temperature °C (continuous):	-40 ... 60 °C
Temperature °F (short term):	-40 ... 175 °F
Temperature °F (continuous):	-40 ... 140 °F

**Accessories:**

C-MP	Mounting plate
------	----------------

