

PICCOLO ABS H 95 G



Sample photo

Order symbol: ABS H 95 G
Product nbr: 8784315
Description: Enclosure, ABS
Remarks: Grey cover

EAN: 6418074002297
EI. number:
 Finland: 3423467
 Electric No. 8212001970
 Denmark:
 Electric No. Italy: 7211050
 Electric No. Sweden: 2536726

Including: Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

Dimensions:	Length	Width	Height	Accessories:
mm:	170	140	95	CHM-3 DIN-35 Mounting rail
inch:	6.7	5.5	3.7	DH-3 DIN-35 Mounting rail
				FP 22046 Wall fastening lug (4 pcs)

Materials:	Rating:
Material: ABS	Ingress Protection (EN 60529): IP66/IP67
Base colour: RAL 7035 -light grey	Impact Resistance (EN 62262): IK07
Cover screws material: Polyamide	Electrical insulation: Totally insulated
Cover colour: RAL 7035 -light grey	Halogen free (DIN/VDE 0472, Part 815): 1
Cover screws colour: Grey	Flammability Rating: UL 94 HB
Gasket material: Polyurethane	Glow Wire Test (IEC 695-2-1) °C: 650
	NEMA Class: NEMA 1, 4X, 6, 12, 13

Temperatures:
Temperature °C (short term): -40 ... 80 °C
Temperature °C (continuous): -40 ... 60 °C
Temperature °F (short term): -40 ... 175 °F
Temperature °F (continuous): -40 ... 140 °F

Accessories:
H-MP Mounting plate

