

PICCOLO ABS H 95 T



Sample photo

Order symbol: ABS H 95 T
Product nbr: 8784015
Description: Enclosure, ABS
Remarks: Transparent cover

EAN: 6418074002280
EI. number:
 Finland: 3423567
 Electric No. 8212001983
 Denmark:
 Electric No. Italy: 7212050
 Electric No. Sweden: 2536756

Including: Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

Dimensions:	Length	Width	Height	Accessories:	
mm:	170	140	95	CHM-3	DIN-35 Mounting rail
inch:	6.7	5.5	3.7	DH-3	DIN-35 Mounting rail
				FP 22046	Wall fastening lug (4 pcs)

Materials:		Rating:
Material:	ABS	Ingress Protection (EN 60529): IP66/IP67
Base colour:	RAL 7035 -light grey	Impact Resistance (EN 62262): IK07
Cover screws material:	Polyamide	Electrical insulation: Totally insulated
Cover colour:	Clear transparent	Halogen free (DIN/VDE 0472, Part 815): 1
Cover screws colour:	Grey	Flammability Rating: UL 94 HB
Gasket material:	Polyurethane	Glow Wire Test (IEC 695-2-1) °C: 650
		NEMA Class: NEMA 1, 4X, 6, 12, 13

Temperatures:	
Temperature °C (short term):	-40 ... 80 °C
Temperature °C (continuous):	-40 ... 60 °C
Temperature °F (short term):	-40 ... 175 °F
Temperature °F (continuous):	-40 ... 140 °F

Accessories:	
H-MP	Mounting plate

