



Order symbol: PC 21/18-FC3
Product nbr: 7520281
Description: Enclosure, PC
Remarks: Grey screw cover

EAN: 6418074010261
El. number:
Finland: 3438226
Electric No. Sweden: 7520281

Including: Base, terminal compartment cover with PUR gasket and screws for mounting plate/DIN-rail. -3 and -L3 versions: Transparent cover with PUR gasket, hinges, locking devices; FC version: Closed PC frame front plate with PUR gasket and cover screws.

Sample photo

Dimensions:	Length	Width	Height	Accessories:
mm:	213	185	102	FP 21/18 Front plate (aluminium) FC PC 21/18 Frame of PC front plate
inch:	8.4	7.3	4.0	
Materials:	Material: Polycarbonate Base colour: RAL 7035 -light grey Gasket material: EPDM & PUR			Rating:
Temperatures:	Temperature °C (short term): -40 ... 120 °C Temperature °C (continuous): -40 ... 80 °C Temperature °F (short term): -40 ... 250 °F Temperature °F (continuous): -40 ... 175 °F			Ingress Protection (EN 60529): IP65 Impact Resistance (EN 62262): IK07/IK08 Electrical insulation: Totally insulated Halogen free (DIN/VDE 0472, Part 815): 1 UV resistance: UL 508 Flammability Rating: UL 746C 5" Glow Wire Test (IEC 695-2-1) °C: 960 NEMA Class: NEMA 1, 3, 3R, 4X, 12, 13
Accessories:	MP 21/18 Mounting plate	Certificates: SGS Fimko Gost R		

