


# IP44 SOLAR GUARDIAN WALL LIGHT WITH PIR

- Front & rear facing LED light chips provide both functional and ambient illumination
- Automatically turns onto standby glow mode when it gets dark (<30lux) and boosts to full power when occupancy detected
- Perfect for outdoor entrance areas, balconies, paths, decorative garden lighting, and sheds/outhouses
- IP44 rated with durable impact resistant housing. No wiring, easy & simple installation



**4000K**  
NEUTRAL  
WHITE

**25,000**  
HOURS

**WHITE/  
BLACK**  
FINISH

**IP44**  
RATED

CAT NO.	DESCRIPTION	LUMINAIRE LUMENS	WATTAGE	EFFICACY Llm/W
LEXS30B30-01	Black	180	1.5W	120
LEXS30W30-01	White	180	1.5W	120

	LENGTH (mm)	WIDTH (mm)	HEIGHT / DEPTH (mm)	WEIGHT (kg)	L FIXING CENTRES (mm)	W FIXING CENTRES (mm)	CEILING CUTOUT (mm)	LUMINAIRE LUMENS (Llm)	LUMINAIRE WATTAGE (W)	EFFICACY (Llm/W)	CCT (K)	CRI	UGR	IP RATED	IK RATED	GLOW WIRE (°C)	RAL COLOUR	TEMP RANGE (°C)	RATED LIFE (HR)	AMBIENT TEMP. RATED LIFE (°C)	L AT RATED LIFE	B AT RATED LIFE	VOLTAGE RANGE	FREQUENCY	EMERGENCY PACK CODE	WARRANTY (YEARS)
LEXS30B30-01	152	96	83	0.25	-	-	-	180	1.5	120	4000 +4000	80	-	IP44	N/A	-	-	0-45	25,000	-	-	-	-	3.7hz	N/A	1
LEXS30W30-01	152	96	83	0.25	-	-	-	180	1.5	120	4000 +4000	80	-	IP44	N/A	-	-	0-45	25,000	-	-	-	-	3.7hz	N/A	1