

DCK2059D2T-GB

DCD777 Compact Drill Driver



- NEW 18V XR Li-Ion Brushless Compact Drill Driver
- 13 mm single sleeve chuck and spindle lock
- Two speed settings, variable speed and reverse switch
- Intelligent trigger design allows for total control
- 16 Position adjustable torque control
- Bright white LED with delay feature
- Improved ergonomic design and rubber grip
- Part of the intelligent XR Lithium Ion Series
- 65Nm hard joint torque
- 340w power output
- No load speed: 0-500/0-1750
- Max Drilling Capacity (wood) 30mm
- Max Drilling Capacity (metal) 13mm

DCB113 Charger

- XR multi-voltage charger
- 2amp charge rate

DCF787 Compact Impact Driver



- NEW 18V XR Li-Ion Brushless Compact Impact Driver
- Intelligent trigger design allows for total control
- Bright white LED with delay feature
- Improved ergonomic design and rubber grip
- Part of the intelligent XR Lithium Ion Series
- 280w power out
- 170Nm max torque
- No Load Speed: 0-2800 RPM
- Impact rate: 0-3200 IPM
- Max bolt diameter M12
- Bit Holder 6.35mm (1/4") hex

DCK2059D2T-GB	Dimensions
Length	44 cm
Width	35 cm
Height	15.5 cm
Weight	5.79 kg
Barcode	5035048666272