




Type 'K' Fine Gauge Bare Wire Thermocouple - Fast response – 0.001" (0.025mm) wire with welded tip x 200mm long



- Ultra-fine Type K welded tip Thermocouple
- 0.001" (0.025mm) fine gauge bare wire x 200mm long
- Optimum Sensitivity
- Very fast response to a fraction of a second
- Ideal for minimal invasive temperature sensing

Specifications

Sensor type: Thermocouple Type 'K'
Wire diameter: 0.001" (0.025mm)
Wire Length: 200mm

T/C Type	Diameter	Length	Order Number
K	0.001"/0.025mm	200mm	XF-1236-FAR

About Labfacility

Formed in 1971, Labfacility specialize in the field of Temperature and Process Measurement.

We are the largest UK manufacturer of both temperature sensors and thermocouple connectors.

Quality & Service

Quality and Service are key elements in the continued growth of Labfacility.

Technical support is always freely available from our experienced technical sales teams and the company has ISO9001 accreditation.

Contact Details

Email
sales@labfacility.com

Website
www.labfacility.com