

LABFACILITY

TEMPERATURE & PROCESS TECHNOLOGY

IEC Glassfibre Exposed Welded Tip Thermocouples with Miniature Thermocouple Plug



- Thermocouple types K & J
- Fast response, welded exposed junction
- Various lengths of glassfibre insulated flat pair cable
- Good temperature resistance (not suitable in fluids)
- 1/0.3mm conductors
- 'Re-Wireable' miniature flat pin plug
- Temperature range -60°C to +350°C (short periods up to 400°C)
- Tolerance to IEC 584 Class 2
- Colour code to IEC 584-3
- Ideal for test & development applications

T/C Type	Conductors	Length	Termination	+Positive tail wire	-Negative tail wire	order code
'K'	1/0.3mm	1 m	Mini plug	Green	White	XF-1211-FAR
'K'	1/0.3mm	5 m	Mini plug	Green	White	XF-1208-FAR
'K'	1/0.3mm	10 m	Mini plug	Green	White	XF-1209-FAR
'J'	1/0.3mm	2 m	Mini plug	Black	White	XF-1204-FAR

About Labfacility

Formed in 1971, Labfacility specialize in the field of Temperature and Process Measurement.

We are the largest UK manufacturer of both temperature sensors and thermocouple connectors.

Quality & Service

Quality and Service are key elements in the continued growth of Labfacility.

Technical support is always freely available from our experienced technical sales teams and the company has ISO9001 accreditation.

Contact Details

Email
sales@labfacility.com

Website
www.labfacility.com