



Main

| | |
|-----------------------------|--|
| Range | Spacial |
| Product name | Spacial CRN |
| Device application | Multi-purpose |
| Product or component type | Compact enclosure |
| Enclosure nominal height | 200 mm |
| Enclosure nominal width | 200 mm |
| Enclosure nominal depth | 150 mm |
| Installation accessory type | Wall-mounting |
| Device composition | Lock 1 Door 1 Body 1 Cable gland plate 2 top and bottom |
| Door type | Plain |
| Mounting plate description | Without mounting plate |

Complementary

| | |
|-----------------------------|--|
| Variant particularity | Sides made from a single folded section Back welded with double profile forming a protected sealed area |
| Number of doors | 1 front face |
| Door opening side | Reversible 120 ° |
| Lock type | 3 mm double-bar lock |
| Type of gland plate | Standard |
| Accessibility for operation | Front |
| Removable parts | Door by hinges Cable gland plate by screws |
| Material | Steel for body |
| Surface finish | Epoxy-polyester powder |
| Colour | Grey RAL 7035 |
| Standards | IEC 62208 |

| | |
|------------------------|-----------|
| Product certifications | UL CUL |
|------------------------|-----------|

Environment

| | |
|-------------------------|------------------------------|
| IP degree of protection | IP66 conforming to IEC 60529 |
| IK degree of protection | IK10 conforming to IEC 62262 |

Offer Sustainability

| | |
|----------------------------------|---|
| Sustainable offer status | Green Premium product |
| RoHS (date code: YYWW) | Compliant - since 0940 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity |
| REACH | Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold |
| Product environmental profile | Available Product environmental |
| Product end of life instructions | Need no specific recycling operations |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|