

Product data sheet  
Characteristics

# NSYCRN54150

Spacial CRN plain door w/o mount.plate.  
H500xW400xD150 IP66 IK10 RAL7035..



## Main

|                             |   |
|-----------------------------|---|
| Range                       | Spacial   |
| Product name                | Spacial CRN                                       |
| Device application          | Multi-purpose                                     |
| Product or component type   | Compact enclosure                                 |
| Enclosure nominal height    | 500 mm  |
| Enclosure nominal width     | 400 mm  |
| Enclosure nominal depth     | 150 mm  |
| Installation accessory type | Wall-mounting                                     |
| Device composition          | Lock 1<br>Door 1<br>Body 1<br>Cable gland plate 1 |
| Door type                   | Plain   |
| Mounting plate description  | Without mounting plate                            |

## Complementary

|                             |  |
|-----------------------------|--|
| Variant particularity       | Sides made from a single folded section<br>Back welded with double profile forming a protected sealed area |
| Number of doors             | 1 front face   |
| Door opening side           | Reversible 120 °   |
| Lock type                   | 3 mm double-bar lock   |
| Type of gland plate         | Standard   |
| Accessibility for operation | Front  |
| Removable parts             | Door by hinges<br>Cable gland plate by screws  |
| Material                    | Steel for body   |
| Surface finish              | Epoxy-polyester powder   |
| Colour                      | Grey RAL 7035  |
| Standards                   | IEC 62208  |

|                        |           |
|------------------------|-----------|
| Product certifications | UL<br>CUL |
|------------------------|-----------|

## Environment

|                         |                              |
|-------------------------|------------------------------|
| IP degree of protection | IP66 conforming to IEC 60529 |
| IK degree of protection | IK10 conforming to IEC 62262 |

## Offer Sustainability

|                                  |   |
|----------------------------------|---|
| Sustainable offer status         | Green Premium product   |
| RoHS (date code: YYWW)           | Compliant - since 0940 - Schneider Electric declaration of conformity<br><a href="#">Schneider Electric declaration of conformity</a> |
| REACH                            | Reference not containing SVHC above the threshold<br><a href="#">Reference not containing SVHC above the threshold</a>                |
| Product environmental profile    | Available<br><a href="#">Product environmental</a>  |
| Product end of life instructions | Need no specific recycling operations   |

## Contractual warranty

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|