

General Information

Kit Part Number:	76650-0054
Description:	Panel Mount Plug and Receptacle, 6 Circuit
Application:	Consumer Products, White Goods Application
Connector Family:	Standard .093
Solution:	Power Connectors
Connector Type:	Wire-to-Wire
Number of Pieces:	32
RoHS:	Yes

Specifications

Adapter Family:	6
Current Rating:	5A
Mounting Style:	Panel Mount
Orientation:	Receptacles, Plugs
Pitch:	5.03mm (.198")
Tool Included:	No
Voltage Rating:	600V
Wire Gauge (AWG):	22-18

Product Highlights

Product Highlights

The Standard .093" (2.36mm) is a durable and economical power or signal connector, capable of carrying up to 12 amps per circuit. Tough Nylon housings and robust terminal design create a durable, long lasting product. The Standard .093" products are reliable and offer high value in features and price. These products are an excellent choice for power or signal interconnect applications.

Features and Benefits

- Male and female terminals may be used in either plug or receptacle housings
- Free hanging or panel mount housing version available
- Round terminals may be oriented in any direction for fast assembly

Applications

- Power Supplies
- Appliances
- Gaming Machines
- Vending Machines
- Refrigerators
- Washing Machines
- Copy Machines

Bill of Materials

Part No.	Qty In Kit	Description	Datasheet	P/N Details	Search Distributors Inventory
02-09-1119	14	2.36mm (.093") Diameter Crimp Female Socket Terminal, 22-18 ...	Datasheet	Details	Search
02-09-2118	14	.093" Diameter Crimp Male Pin Terminal, 22-18 AWG	Datasheet	Details	Search
03-09-1061	2	6 Circuit, Panel Mount Nylon Connector Receptacle	Datasheet	Details	Search
03-09-2061	2	6 Circuit, Panel Mount Nylon Connector Plug	Datasheet	Details	Search

Recommended Tool

Part No.	Included in Kit
63819-1200	No
11-02-0003	No
63824-0200	No
11-03-0006	No




76650-0054

**RoHS
COMPLIANT**

.093" SERIES

.093" 6 Circuit Conn W/Recpt & Plug

5 Amps/600 Volts UL & CSA Recognized



Waldom
ELECTRONICS

www.molexkits.com