



Model #: CPS425SL

UPC: 649532004256

MSRP: \$42.99



## Title

CPS425SL UPS - 425VA/230W 6-Outlet RJ11 Compact Design EMI/RFI USB/Serial

## Description

The CPS425SL Home and Office Series UPS system is perfect power protection for individuals running a stand-alone PC in their home or office. It includes PowerPanel™ Power Management software which monitors the vitals of the CyberPower battery backup system and will safely shut down your system in case of a power outage. Composite IC circuitry offers advanced lightning protection and also guards against surges, spikes, sags, brownouts and other power abnormalities. This rugged unit is equipped with a RJ11 port which protects against surges from phone or network disruptions. The unit is also perfect for protecting other electronics such as monitors, printers, scanners, speakers, fax machines, CD/DVD players, and iPods.

## Features

- EMI/RFI - Provides shielding against electromagnetic interference & radio frequency signals. Most commonly, this is used to prevent line noise or “humming” that occurs over telephone lines or stereo electronics.
- Transformer-spaced Outlets - Widely spaced outlets allow you to conveniently add large transformer-based plugs without compromising the utility of other outlets.
- PowerPanel™ Power Management Software – In the event of a power outage, PowerPanel will safely save and close your open files and shut your computer down in an orderly, intelligent manner. It also features adjustable battery run times, popup warning messages, event logging, and scheduled shutdowns.
- LED Indicators - LED status lights indicate Power-On and wiring faults.
- Audible Alarms - Audible tones identify when the unit is running off of battery power, unit overloads and low battery.
- Convenient Mounting – Multiple mounting options: horizontal, vertical, cabinet, and wall.
- Resettable Circuit Breaker - Convenient unit reset switch in case of an overload.
- 3-year Warranty - CyberPower will replace damaged units if within 3 years of purchase date. We stand behind our products and guarantee quality. CyberPower also offers a #1 rated technical support team that will assist you with product, installation, or warranty concerns --- Free of Charge!
- ISO & Safety Certifications - All CyberPower's manufacturing facilities are ISO-9001 Quality Tested. Our products are also certified by the FCC, cUL, and UL.
- Windows™ Compliant - Our Power Management software has been fully tested and compliant with Windows 9x, 200x, Server, and XP.

## Technical Specifications

<b>Technical Information</b>	
Product Type	Standby UPS
Plug/Connector Type	NEMA 5-15P
Receptacles	6 Total Receptacles <ul style="list-style-type: none"> <li>• 3 x NEMA 5-15R - Backup/Surge-protected</li> <li>• 3 x NEMA 5-15R - Surge-protected</li> </ul>
Switching Time	4 ms
Dataline Protection	1 x RJ11 (One-in/Two-out)
Automatic Voltage Regulation	No
<b>Power Description</b>	
Load Capacity	425VA / 230W
Input Voltage	110V AC
Input Voltage Range	100V AC to 140V AC Single-phase
Output Voltage	120V AC Single-phase
Frequency	<ul style="list-style-type: none"> <li>• 57 to 63Hz Input</li> <li>• 59 to 61Hz Output</li> </ul>
Voltage Handling	5%
Waveform Type	Simulated Sine Wave
Surge Energy Rating	585J
Filtering	EMI/RFI
Circuit Breaker	1 x 15A
<b>Management</b>	
Overload Protection	<ul style="list-style-type: none"> <li>• On Utility: Circuit Breaker</li> <li>• On Battery: Internal Current Limiting</li> </ul>
Audible Alarms	<ul style="list-style-type: none"> <li>• Low Battery</li> <li>• On Battery</li> <li>• Overload</li> </ul>
Bypass Switch	Not Provided
Emergency Power OFF	No
<b>Controls/Indicators</b>	
Status Indicators	<ul style="list-style-type: none"> <li>• Power On</li> <li>• Wiring Fault</li> </ul>
<b>Interfaces/Ports</b>	
Interfaces/Ports	<ul style="list-style-type: none"> <li>• 1 x DB-9 RS-232 Serial with optional USB Adapter</li> </ul>
<b>Battery Information</b>	
Batteries	1 x 12V/4.5Ah Maintenance Free Sealed Lead-acid
Backup/Run Time	<ul style="list-style-type: none"> <li>• 2 Minute(s) 230W Full-load</li> <li>• 9 Minute(s) 115W Half-load</li> <li>• Entry-level PC with 19" LCD (150W) - 7 minutes</li> </ul>
Battery Life	3 Year(s) to 6
Battery Recharge Time	8 Hour(s)

<b>Environmental Conditions</b>	
Temperature	<ul style="list-style-type: none"> <li>• 32 °F (0 °C) to 95 °F (35 °C) Operating</li> <li>• 5 °F (-15 °C) to 113 °F (45 °C) Non-operating</li> </ul>
Humidity	<ul style="list-style-type: none"> <li>• 0 to 95% Non-condensing Operating Humidity</li> <li>• 0 to 95% Non-condensing Non-operating</li> </ul>
Altitude	<ul style="list-style-type: none"> <li>• 0 ft to 10000 ft Operating</li> <li>• 0 ft to 50000 ft Non-operating</li> </ul>
<b>Physical Characteristics</b>	
Color	Black
Form Factor	Multi-mount Tower
Power Cord/Cable	6 ft
Dimensions	6.25" Height x 9.75" Width x 3.25" Depth
Shipping Dimensions	9" Height x 14.25" Width x 4.5" Depth - Display Box
Weight	8.6 lb
Shipping Weight	9.7 lb - Display Box
<b>Miscellaneous</b>	
Package Contents	<ul style="list-style-type: none"> <li>• UPS Unit</li> <li>• User Manual</li> <li>• Power Management Software</li> <li>• Warranty Card</li> <li>• Serial Cable</li> <li>• Phone Cable</li> </ul>
Certifications & Standards	<ul style="list-style-type: none"> <li>• FCC Class B certified</li> <li>• cUL</li> <li>• UL 1778</li> </ul>
Software Included	PowerPanel
Country of Origin	China
Identical Model #s	AE425
<b>Warranty</b>	
Standard Warranty	3 Year(s) Parts & Labor
Additional Warranty Information	<ul style="list-style-type: none"> <li>• CyberPower stands behind its products by offering an industry leading 3-year warranty. CyberPower also has a #1 rated technical support team that will assist you with product, installation, or warranty concerns --- Free of charge.</li> <li>• Connected Equipment Guarantee of \$35,000</li> </ul>