



Model #: CP550SL

UPC: 649532005505

MSRP: \$59.99



Title

CP550SL UPS - 550VA/330W 8-Outlet RJ11 Compact Design EMI/RFI USB/Serial

Description

The **CP550SL** Home and Office Series Uninterruptible Power Supply (UPS) is perfect power protection for individuals running a stand-alone PC in their home or office. It includes PowerPanel PE™ Power Management software which monitors the vitals of the UPS and will safely shutdown your system in case of a power outage. Composite IC circuitry offers advanced lightning protection and also guards against surges, spikes, sags, brownouts and other power abnormalities. This rugged unit is equipped with a RJ11 port which protects against surges from phone or network disruptions. The small footprint design is ideal for horizontally or vertically placement, and is even designed for wall-mountability. The unit is also perfect for protecting other electronics such as monitors, printers, scanners, speakers, fax machines, CD/DVD players, and iPods.

Features

- EMI/RFI - Provides shielding against electromagnetic interference & radio frequency signals. Most commonly, this is used to prevent line noise or “humming” that occurs over telephone lines or stereo electronics.
- Transformer-spaced Outlets - Widely spaced outlets allow you to conveniently add large transformer-based plugs without compromising the utility of other outlets.
- USB Connectivity - HID compliant USB port enables full integration with built-in power management and auto shutdown features of Windows, Linux and Mac OS X.
- PowerPanel PE™ Smart Management Software – In event of a power outage, PowerPanel PE will not only save your open files and will also “Hibernate” your PC to increase the run-time on the UPS unit. PowerPanel is quickly and easily installed on any Windows-based PC and is designed to utilize minimal system resources. Diagnostic screens give immediate visuals of the UPS’s status, and also include the following features: Silent operation mode, configurable system notifications, automatic self tests, adjustable high/low voltage warnings, event/data logging, and scheduled shutdowns.
- LED Indicators - LED status lights indicate Power-On and wiring faults.
- Audible Alarms - Audible tones identify when the unit is running off battery power, unit overloads and low battery.
- Convenient Mounting – Multiple mounting options: horizontal, vertical, cabinet, and wall.
- Resettable Circuit Breaker - Convenient unit reset switch in case of an overload.
- 3-year Warranty - CyberPower will replace damaged units if within 3 years of purchase date. We stand behind our products and guarantee quality. CyberPower also offers a #1 rated technical support team that will assist you with product, installation, or warranty concerns --- Free of Charge!
- ISO & Safety Certifications - All CyberPower’s manufacturing facilities are ISO-9001 Quality Tested. Our products are also certified by the FCC, cUL, and UL.
- Windows Vista™ Compliant - Our Power Management software has been fully tested and compliant with Windows 9x, 200x, Server, XP, and Vista.

Technical Specifications

Technical Information	
Product Type	Standby UPS
Plug/Connector Type	NEMA 5-15P
Receptacles	6 Total Receptacles <ul style="list-style-type: none"> • 3 x NEMA 5-15R - Backup/Surge-protected • 3 x NEMA 5-15R - Surge-protected
Switching Time	4 ms
Dataline Protection	1 x RJ11 (One-in/Two-out)
Automatic Voltage Regulation	No
Power Description	
Load Capacity	550VA / 330W
Input Voltage	110V AC
Input Voltage Range	100V AC to 140V AC Single-phase
Output Voltage	120V AC Single-phase
Frequency	<ul style="list-style-type: none"> • 57 to 63Hz Input • 59 to 61Hz Output
Voltage Handling	5%
Waveform Type	Simulated Sine Wave
Surge Energy Rating	890J
Filtering	EMI/RFI
Circuit Breaker	1 x 15A
Management	
Overload Protection	<ul style="list-style-type: none"> • On Utility: Circuit Breaker • On Battery: Internal Current Limiting
Audible Alarms	<ul style="list-style-type: none"> • Low Battery • On Battery • Overload
Bypass Switch	Not Provided
Emergency Power OFF	No
Controls/Indicators	
Status Indicators	<ul style="list-style-type: none"> • Power On • Wiring Fault
Interfaces/Ports	
Interfaces/Ports	<ul style="list-style-type: none"> • 1 x DB-9 RS-232 Serial • 1 x USB
Battery Information	
Batteries	1 x 12V/8Ah Maintenance Free Sealed Lead-acid User-replaceable Hot-swappable
Backup/Run Time	<ul style="list-style-type: none"> • 2 Minute(s) 330W Full-load • 13 Minute(s) 165W Half-load • Entry-level PC with 19" LCD (150W) - 14 min. • Midrange PC with 19" LCD (300W) - 5 min.
Battery Life	3 Year(s) to 6
Battery Recharge Time	8 Hour(s)

Environmental Conditions	
Temperature	<ul style="list-style-type: none"> • 32 °F (0 °C) to 95 °F (35 °C) Operating • 5 °F (-15 °C) to 113 °F (45 °C) Non-operating
Humidity	<ul style="list-style-type: none"> • 0 to 95% Non-condensing Operating Humidity • 0 to 95% Non-condensing Non-operating
Altitude	<ul style="list-style-type: none"> • 0 ft to 10000 ft Operating • 0 ft to 50000 ft Non-operating
Physical Characteristics	
Color	Black
Form Factor	Multi-mount Tower
Power Cord/Cable	6 ft
Dimensions	6.25" Height x 10.75" Width x 3.25" Depth
Shipping Dimensions	9" Height x 15.25" Width x 4.5" Depth - Display Box
Weight	11.5 lb
Shipping Weight	12.6 lb - Display Box
Miscellaneous	
Package Contents	<ul style="list-style-type: none"> • UPS Unit • User Manual • Power Management Software • Warranty Card • Serial Cable • Phone Cable
Certifications & Standards	<ul style="list-style-type: none"> • FCC Class B certified • cUL • UL 1778
Software Included	PowerPanel PE
Country of Origin	China
Identical Model #'s	AE550
Warranty	
Standard Warranty	3 Year(s) Parts & Labor
Additional Warranty Information	<ul style="list-style-type: none"> • CyberPower stands behind its products by offering an industry leading 3-year warranty. CyberPower also has a #1 rated technical support team that will assist you with product, installation, or warranty concerns --- Free of charge. • Connected Equipment Guarantee of \$75,000