



**Tripp Lite**  
1111 West 35th Street  
Chicago, IL 60609 USA  
Telephone: +(773) 869 1234  
E-mail: [saleshelp@tripplite.com](mailto:saleshelp@tripplite.com)

## Model #: ECO850LCD

### ECO 850VA Energy-saving 120V Standby UPS with Enhanced LCD interface and USB monitoring port



#### Highlights

- 850VA power saving, ultra-compact, standby UPS with enhanced LCD display
- Interactive LCD user interface offers UPS status and control options with detailed UPS and site electrical information
- 4 built-in ECO outlets save power by automatically turning off connected accessories when the computer is not in use
- 99% line-mode UPS efficiency saves energy and operating costs
- Includes USB port, single line TEL / DSL line surge suppression, space saving right-angle input plug and six surge-only outlets
- Input: NEMA 5-15P (120V 15A) / Output: 12 NEMA 5-15R (120V)
- 3 year product warranty / \$100,000 Ultimate Lifetime Insurance (USA, Puerto Rico & Canada only)

#### Description

The ECO850LCD ultra-compact green UPS offers complete protection from blackouts, voltage fluctuations and transient surges. Interactive LCD user interface offers detailed UPS and site electrical data, including input/output voltage, estimated runtime remaining, load percentage, load wattage and battery charge level. Energy saving ECO outlets give users the option to automatically power off unused desktop accessories like a printer and audio speakers as the computer connected via USB goes to low-power sleep or shutdown modes. 99% full load efficiency rating offers energy savings and cool operating temperatures. Green eco-friendly design meets strict RoHS environmental standards. Provides uninterruptible transfer to battery derived AC output during power failures and voltage fluctuations with enough runtime to save and shutdown connected equipment without data loss. Space saving, ultra-compact desktop or wall mount compatible housing. Includes 6 battery supported outlets for computer, monitor and four vital system accessories, plus 6 additional surge suppression-only outlets for accessories not requiring battery support. Four surge-only outlets marked "ECO" can be configured to automatically power-off within 3 minutes of the connected computer entering sleep or shutdown mode. USB port monitors computer power status for ECO power savings and enables direct integration with built-in power management and auto-shutdown features of Windows and Mac OS X. PowerAlert software is also available via free download from [www.tripplite.com](http://www.tripplite.com) to provide advanced auto-shutdown, UPS monitoring and data saving options. USB cable included. Built-in single line RJ11 phone suppression protects modem, fax machine, cordless phone or other accessories with a dial-up/DSL phone connection. Built-in interactive LCD screen offers continuous power and UPS status information. Audible alarm warns of power failure conditions. Self-test, display brightness, alarm disable and LCD information display scrolling options are controllable via interactive LCD user interface. 850VA / 425 watt UPS capacity supports entry-level PC systems for up to 45 minutes during power fail conditions. 3 year warranty. \$100,000 connected equipment insurance (USA, Puerto Rico, & Canada Only).

#### Package Includes

- ECO850LCD UPS System
- USB cable
- Instruction manual

#### Features

- ECO850LCD power saving, green UPS offers complete protection from blackouts, voltage fluctuations and transient surges
- Interactive LCD user interface with scroll and select buttons offer detailed UPS status and control options
- LCD screen options support continuous display of Input voltage, Output voltage, Estimated runtime, Load percentage, Load wattage and Battery charge percentage – with the option to continuously scroll all six information fields
- LCD screen with scroll and select functions also gives users the ability to enable and disable specific UPS features, such as the ECO energy-saving feature, permanent alarm silence, LCD brightness, information display scroll functions and UPS self-test operation
- Set of 4 optional ECO outlets automatically power off unnecessary computer accessories like a printer, scanner and audio speakers three minutes after computer enters sleep or shutdown mode
- Full load efficiency rating of 99% saves energy and ensures cool operating temperatures
- ECO850LCD emits only 17 BTU/hr. and consumes less than 5 watts once the battery is charged
- Eco-friendly design meets strict RoHS (Restriction of Hazardous Substances) environmental standards

- 850VA / 425 watt UPS provides battery-derived AC output during power failures and severe voltage fluctuations to support an entry level desktop computer up to 45 minutes
- Ultra compact UPS supports a variety of placement options for desktop or wall mount installation
- Includes 6 UPS supported outlets for computer, monitor and two additional vital system peripherals requiring continuous power
- Includes 6 Surge-only outlets for accessories not requiring battery support
- Four of the Surge-only outlets are designated ECO outlets that can be configured to automatically power-off three minutes the connected computer enters low power standby or shutdown mode
- USB port monitors computer power status for ECO power savings and enables direct integration with built-in power management and auto-shutdown features of Windows and Mac OS X
- PowerAlert software is also available via free download from [www.tripplite.com](http://www.tripplite.com) to provide advanced auto-shutdown, UPS monitoring and data saving options
- Single line RJ11 phone suppression jacks protect modem, fax machine, cordless phone or other accessories from surges on dial-up/DSL phone connections
- USB cable included
- Space-saving right angle input plug
- 3 year standard warranty with \$100,000 connected equipment insurance (USA, Puerto Rico & Canada only)

## Specifications

OUTPUT	
Output Volt Amp Capacity (VA)	850
Output Watt Capacity (watts)	425
Nominal Output Voltage(s) Supported	115V; 120V
Frequency compatibility	60 Hz
Output voltage regulation (Battery mode)	115V (+/- 5%)
Built-in UPS output receptacles	12 5-15R outlet(s)
Surge suppression only outlets	6 UPS outlets, 6 surge-only outlets
Output AC waveform (AC mode)	Sine wave
Output AC waveform (battery mode)	PWM sine wave
INPUT	
Rated input current (at maximum load)	10A
Nominal Input Voltage(s) Supported	120V AC
UPS input connection type	5-15P; Right-Angled
Input circuit breaker	10A
UPS Input cord length (ft.)	6
UPS Input cord length (m)	1.8

<b>Recommended Electrical Service</b>	15A 120V
<b>BATTERY</b>	
<b>Full load runtime (minutes)</b>	2.8 min. (425w)
<b>Half load runtime (minutes)</b>	13 min. (210w)
<b>DC system voltage (VDC)</b>	12
<b>LEDS ALARMS &amp; SWITCHES</b>	
<b>Front panel LCD display</b>	Front panel LCD reports Input voltage, Output voltage, Estimated runtime, Load percentage, Load wattage and Battery charge percentage; Also supports configuration of ECO energy-saving feature, alarm silence mode, LCD brightness, information display scrolling and UPS self-test operation
<b>Alarms</b>	Audible alarm indicates power-failure and overload status
<b>Alarm cancel operation</b>	Alarm-cancel switch temporarily silences alarm during a power failure; Silent-alarm mode setting is available as an LCD settable option
<b>Switches</b>	Set of two switches offers complete UPS control; ON / OFF / MODE switch offers UPS power off/on control and LCD screen mode selection; MUTE / SELECT button momentarily silences alarm during a power failure and value selection for LCD interface options
<b>SURGE / NOISE SUPPRESSION</b>	
<b>UPS AC suppression joule rating</b>	420
<b>UPS AC suppression response time</b>	Instantaneous
<b>UPS Dataline suppression</b>	1 line TEL/DSL (1 in / 1 out)
<b>EMI / RFI AC noise suppression</b>	Yes
<b>PHYSICAL</b>	
<b>Installation form factors supported with included accessories</b>	Tower; Ultra-compact desktop; Wallmount (using keyhole mounting tabs)
<b>Primary form factor</b>	Desktop
<b>UPS / Power Module dimensions in primary form factor (height x width x depth / inches)</b>	3.5 x 12 x 7
<b>UPS / Power Module dimensions in primary form factor (height x width x depth / cm)</b>	8.9 x 30.5 x 17.8
<b>UPS / Power Module weight (lbs)</b>	9.5
<b>UPS / Power Module weight (kg)</b>	4.3
<b>UPS Shipping dimensions (height x width x depth / inches)</b>	4.5 x 15 x 10

<b>UPS Shipping dimensions (height x width x depth / cm)</b>	11.4 x 38.1 x 25.4
<b>Shipping weight (lbs)</b>	10.25
<b>Shipping weight (kg)</b>	26
<b>UPS housing material</b>	Plastic
<b>ENVIRONMENTAL</b>	
<b>Operating Temperature Range</b>	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
<b>Storage Temperature Range</b>	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
<b>Relative Humidity</b>	0 to 95%, non-condensing
<b>AC mode BTU / hr. (full load)</b>	17
<b>COMMUNICATIONS</b>	
<b>Communications interface</b>	USB (HID enabled)
<b>PowerAlert software</b>	Free download from <a href="http://www.tripplite.com">www.tripplite.com</a>
<b>Communications cable</b>	USB interface cable included
<b>WatchDog compatibility</b>	Supports Watchdog application, OS and hard-reboot restart options for remote applications
<b>LINE / BATTERY TRANSFER</b>	
<b>Transfer time</b>	AC to battery mode: 6 milliseconds / Battery to AC mode: 3 milliseconds
<b>Low voltage transfer to battery power (setpoint)</b>	99
<b>High voltage transfer to battery power (setpoint)</b>	139
<b>SPECIAL FEATURES</b>	
<b>Cold Start (startup in battery mode during a power failure)</b>	Cold-start operation supported
<b>Green &amp; high efficiency features</b>	Greater than 95% efficiency - GREEN UPS; Power saving auto-shutoff ECO outlets
<b>CERTIFICATIONS</b>	
<b>UPS Certifications</b>	Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Meets FCC Part 15 Category B (EMI); Meets FCC Part 68 / Industrie Canada (telecommunic; ROHS (Restriction of Hazardous Substances)
<b>WARRANTY</b>	
<b>Product Warranty Period (U.S., Canada &amp; Puerto Rico)</b>	3-year limited warranty
<b>Connected Equipment Insurance (U.S., Canada &amp; Puerto Rico)</b>	\$100,000 Ultimate Lifetime Insurance

---

## Related Items

### Optional Products

Product Type	Related Model	Description	Qty.
Extended Warranties	<a href="#">WEXT5-INTERNET</a>	5-Year Extended Warranty - For Internet Office, AVR and ECO Series UPS Systems	-
Power Cables	<a href="#">P007-002</a>	2-ft. Heavy-Duty 14AWG Power cord (IEC-320-C13 to NEMA 5-15P)	-
Power Cables	<a href="#">P007-006</a>	6-ft. Heavy-Duty 14AWG Power cord (IEC-320-C13 to NEMA 5-15P)	-
Power Cables	<a href="#">P007-010</a>	10-ft. Heavy-Duty 14AWG Power cord (IEC-320-C13 to NEMA 5-15P)	-
Power Cables	<a href="#">P010-012</a>	12-ft. 18AWG Power cord (NEMA 5-15P to IEC-320-C13)	-
Power Cables	<a href="#">P022-001</a>	1-ft. 18AWG Power Extension cord (NEMA 5-15R to NEMA 5-15P)	-
Power Cables	<a href="#">P023-001</a>	1-ft. 14AWG Power Adapter cord (NEMA L5-15R to NEMA 5-15P)	-

More information, including related products, owner's manuals, and additional technical specifications, can be found online at [www.tripplite.com/en/products/model.cfm?txtModelID=4862](http://www.tripplite.com/en/products/model.cfm?txtModelID=4862).

---

Copyright © 2011 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.