



Tripp Lite
 1111 West 35th Street
 Chicago, IL 60609 USA
 Telephone: +(773) 869 1234
 E-mail: saleshelp@tripplite.com

Model #: SK3-0

3 Outlet, Direct Plug-In, 660 Joules - Protect It! Surge Suppressor

Highlights

- 3 outlets/direct plug-in
- 660 joule rating
- Diagnostic LEDs
- \$5,000 Ultimate Lifetime Insurance (USA & Canada only)



Description

The SK3-0 surge suppressor offers reliable surge and line noise protection. The compact direct plug-in design allows for easy portability and features 3 outlets and 660 joules of surge energy absorption. Diagnostic LEDs alert you to potential wiring or protection faults before connected equipment is damaged. \$5,000 Ultimate Lifetime Insurance (USA & Canada only).

Applications

- Ideal for any desktop, network or home computing application requiring AC protection

Package Includes

- SK3-0 surge suppressor

Features

- 3 outlets / direct plug-in
- Surge suppression rating: 660 joules
- EMI/RFI noise filtering
- Diagnostic LEDs indicate Protected (green) & Grounded (red)
- Lifetime product warranty
- \$5,000 Ultimate Lifetime Insurance (USA & Canada only)

Specifications

OVERVIEW	
Intended Application	Home/Office
OUTPUT	
Frequency compatibility	60 Hz
Output watts	1875
Circuit Breaker (amps)	15
Outlet quantity / type	3 NEMA 5-15P

INPUT	
Recommended Electrical Service	120V
Input connection type	NEMA 5-15P input plug
Input plug features	120V, 15A
Input cord length details	Direct Plug-In
Voltage compatibility (VAC)	120
SURGE / NOISE SUPPRESSION	
AC suppression joule rating	660
AC suppression response time	< 1ns
Protection modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
Clamping voltage (RMS)	150
AC suppression surge current rating	27,000
UL1499 let through rating	500, 400, 500
Immunity	Conforms to IEE 587/ANSI C62.41
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Unit Dimensions (HWD/in)	2.5 x 3.8 x 2.1
Unit Dimensions (HWD/cm)	6.35 x 9.7 x 5.33
Unit weight (lbs)	.20
Unit weight (kg)	.09
Material of construction	Plastic
Integrated keyhole mounting tabs	Direct plug-in suppressor mounts directly to a wall receptacle
Receptacle Color	Gray
Style	Direct plug-in
CERTIFICATIONS	
UL1449 3rd Edition (AC Suppression)	UL1449 3rd Edition
Approvals	RoHS
WARRANTY	
Product Warranty Period (U.S., Canada & Puerto Rico)	Lifetime limited warranty

**Connected Equipment
Insurance (U.S., Canada &
Puerto Rico)**

\$5,000 [Ultimate Lifetime Insurance](#)

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=4981.

Copyright © 2011 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.