



Model #: 750

UPC: 649532007509

MSRP: \$17.99



## Title

750 7-Outlet Surge Suppressor - 1250 Joules 15A RJ11 EMI/RFI Right-angle

## Description

The CyberPower 750 surge suppressor is a Home/Office Computer Surge Protector and is fully internet-ready with 1-in / 2-out phone/fax/modem protection. This model is ideal for personal computers, phones/fax/modems, printers, stereos, and CD/DVD players. 1250 joule MOV technology safely guards the surge suppressor and connected electronics against line abnormalities and lightning surges. EMI/RFI filtering blocks unwanted line noise from all connected electronics. CyberPower fully stands behind its products with a lifetime product warranty and Connected Equipment Guarantee of \$75,000.

## Features

- MOV (Metal Oxide Varistor) - MOV technology allows normal current to pass through the device, while diverting any surge/spikes through the ground circuit. This safely protects all connected electronics along with the surge suppressor itself.
- Built-In Automatic Shutdown - In the event that the surge/spike exceeds the unit's ability to suppress the signal, the CyberPower surge suppressor will safely shut itself down to protect all connected electronics.
- Transformer-spaced Outlets - Widely spaced outlets allow you to conveniently add large transformer-based plugs without compromising the utility of other outlets.
- EMI/RFI Shielding - Provides shielding against electromagnetic interference & radio frequency signals. Most commonly, this is used to prevent line noise or "humming" that occurs over telephone lines or stereo electronics.
- ISO & Safety Certifications - All CyberPower's manufacturing facilities are ISO-9001 Quality Tested. Our products are also UL Listed and CSA Certified.
- Keyhole Mounting Slots - Convenient mounting slots are located on the back on the surge suppressor.
- Sturdy ABS Case - Constructed of impact-resistant composite material for maximum durability.

## Technical Specifications

<b>Technical Information</b>	
Plug/Connector Type	NEMA 5-15P, Right Angle
Receptacles	7 x NEMA 5-15R
Dataline Protection	<ul style="list-style-type: none"> <li>• RJ-11 Phone/Modem/DSL/Fax/Cordless Phone (One-in/Two-out)</li> </ul>
Protection	<ul style="list-style-type: none"> <li>• H-N Line: 30kVA</li> <li>• H-G Line: 14.5kVA</li> <li>• N-G Line: 14.5kVA</li> <li>• Response Time: &lt;1ns</li> <li>• Clamping Voltage: 330V</li> <li>• Attenuation: Up to 58dB</li> </ul>
<b>Power Description</b>	
Input Voltage	110 V AC to 120 V AC $\pm$ 5%
Output Voltage	120 V AC
Current	15A
Frequency	60 Hz
Power Handling	59kVA
Surge Energy Rating	2800J
Filtering	EMI/RFI 150KHz to 100MHz
Circuit Breaker	1 x 15A Resettable
Power Switch	Rocker Switch
<b>Controls/Indicators</b>	
Status Indicators	<ul style="list-style-type: none"> <li>• 1 x Power (Red)</li> <li>• 1 x Surge (Red)</li> <li>• 1 x Ground (Green)</li> </ul>
<b>Physical Characteristics</b>	
Power Cord/Cable	6 ft
Color	Black
Form Factor	Floor/Wall mountable
Dimensions	2.5" Height x 12" Width x 1.5" Depth
Shipping Dimensions	14.5" Height x 7" Width x 2" Depth - Display Box
Weight	1.475 lb
Shipping Weight	1.625 lb - Display Box
<b>Miscellaneous</b>	
Package Contents	<ul style="list-style-type: none"> <li>• 750 Surge Unit</li> <li>• Manual</li> <li>• 6' RJ-11 Cord</li> </ul>
Certifications & Standards	<ul style="list-style-type: none"> <li>• UL Listed , CSA Certified</li> </ul>
Country of Origin	China
<b>Warranty</b>	
Standard Warranty	CyberPower will 100% guarantee this product for <u>as long as you own it!</u> We stand behind our products and guarantee quality. CyberPower also offers a #1 rated technical support that will assist you with product, installation, or warranty concerns --- Free of Charge.
Connected Equipment Guarantee	\$75,000