

MODEL TL-5920/B



For Utility Metering Applications

TECHNICAL DATA

(Typical values @+ 25°C for batteries stored for one year or less)



- Nominal capacity @ 3 mA, to 2 V 8.5 Ah
- Rated voltage 3.6 V
- Maximum recommended continuous current 230 mA
- Maximum pulse current capability 400 mA
- Weight 55 g (1.94 oz)
- Operating temperature range -55 °C to +85 °C
- Li metal content approx. 2.5 g
- U.L. Component Recognition, MH 12193

TADIRAN LITHIUM BATTERIES



ADDITIONAL INFORMATION

CONNECTOR TYPE:	
HOUSING	MOLEX 5057-9004
CONTACTS	MOLEX 1602-0088
POLARITY KEY	MOLEX 1504-0293
CATALOGUE NO.	15-5920-80000



iXtra - Long Term High Performance

Note: Any presentations in this data sheet concerning performance are for information purpose only and are not construed as warranties either expressed or implied, of future performance. ECN 1502099 Rev. D 03/2010