

# HA8-3 | HA4-3 | HA8

## HDMI™ Distribution Amplifier With HDSTAY



HA8-3



HA4-3



HA8



HDMI™ Cable Retention Bracket

### KEY FEATURES

HDMI™ A/V Distribution Amplifier  
 Our 1 in 4 out or 1 in 8 out HDMI™ (Deep Color) Distribution Amplifier and distribute one high definition source to multiple displays

- Enhanced amplified signals for longer cable runs
- Compliant with HDMI™/HDCP\* requirements
- Supports high-resolution displays of UXGA, 480i, 480p, 720p, 1080i, 1080p
- Cascadable to multiple amplifiers for large TV displays
- Secure HDMI™ connection with integrated cable retention bracket
- HA8-3 & HA4-3 compliant with HDMI™ V1.3b (Deep Color up to 12 bit)

### SPECIFICATIONS

#### HA8-3: Deep Color

HDMI™ <b>Input</b> Connector (A-Type Female):	1	LED indicators for port activity
HDMI™ <b>Output</b> Connector (A-Type Female):	8	
Max. Resolution:	1080p (12 Bit)	
Cable Distance (Device to Monitor):	10 m (Max.)	
Signal Type:	Standard HDMI™	
Power Adapter (Min.):	AC100-240V (5VDC/4A)	
Housing:	Metal	
Weight:	3.5 lbs.	
Dimensions (L x W x H):	15.8" x 1.5" x 6.4"	

#### HA4-3: Deep Color

HDMI™ <b>Input</b> Connector (A-Type Female):	1	LED indicators for port activity
HDMI™ <b>Output</b> Connector (A-Type Female):	4	
Max. Resolution:	1080p	
Cable Distance (Device to Monitor):	10 m (Max.)	
Signal Type:	Standard HDMI™	
Power Adapter (Min.):	AC100-240V (5VDC/4A)	
Housing:	Metal	
Weight:	2.2 lbs.	
Dimensions (L x W x H):	14.95" x 1.5" x 6.8"	

#### HA8: 8-Bit color

HDMI™ <b>Input</b> Connector (A-Type Female):	1
HDMI™ <b>Output</b> Connector (A-Type Female):	8
Max. Resolution:	1080p (8 Bit)
Cable Distance (Device to Monitor):	10 m (Max.)
Signal Type:	Standard HDMI™
Power Adapter (Min.):	AC100-240V (5VDC/4A)
Housing:	Metal
Weight:	3.5 lbs.
Dimensions (L x W x H):	15.7" x 1.5" x 6.5"