


**PARAMETERS**

Impedance	8 Ohm
Re	7.2 ohms
Le	0.88 mH
Fs	93.8Hz
Qms	2.56
Qes	1.15
Qts	0.79
Mms	6.84g
Cms	0.42mm/N
Sd	55.4cm <sup>2</sup>
BL	5.01Tm
Vas	1.84liters
Xmax	2.5mm
VC diameter	1"
SPL	85dB
RMS power	40Watts
Frequency Response	94 to 10,000Hz

**SPL vs Freq**



**Impedance vs Freq**

