

# LTD2304SS-B 4 CH D1 Realtime with HDMI High Performance DVR

## Features

- Real-Time High Resolution Recording
- H.264 Compression Technology
- Intuitive Graphic User Interface
- Quick Search, Easy Backup
- Remote Monitoring / Control via CMS or Web Browsers
- Multi-User management
- Live View on Smart Phones and Playback on iPhones
- 2 Year Warranty & Free Life-Time Technical Support



## Specifications

<b>System</b>	Compression Format	H.264
	OS	Embedded Linux
<b>Video</b>	Input	4CH, BNC (1.0Vp-p, 75Ω)
	VGA Output	1*VGA:1280x1024, 800x600, 1024x768
	BNC	1*BNC Mainout
	Loop Output	NO
	Spot Output	NO
	HDMI	YES
<b>Audio</b>	Audio Input	2CH
	Audio Output	1CH
<b>Recording</b>	Bidirectional Talk	YES
	Real Time Recording	4 CH D1
	D1	30(NTSC)/225(PAL)fps
	CIF	120(NTSC)/100(PAL)fps
	Recording Mode	Schedule, Manual, Motion Detection
<b>Playback</b>	Playback Channel	4CH
	Search Mode	Time, Event, File Management
<b>Backup</b>	USB Disk	1 USB2.0 port for portable HDD
	DVD Burner	-
	Backup Format	DAT or AVI
<b>Dual Steam</b>	Master Stream	30(NTSC)/25(PAL)fps CIF per Ch
	Network Stream	1/2 fps CIF per Ch
<b>Remote Application</b>	Browser	IE (windows XP/vista/7), Safari(Mac OS), Chrome, Firefox
	CMS	YES
	Mobile Phone OS	SuperCam/pro/HD for iPhone(iPad/iPad2)/Blackberry/Android
	User Access	10 users online with professional authority management
<b>Alarm</b>	Alarm Input	-
	Alarm Output	-
<b>Storage</b>	HDD (Each max. size 2 TB)	1x SATA
	e-SATA	NO
	Max HDD after Deploying DVD Writable Driver	-
<b>PTZ</b>	PTZ	1*RS485
	PTZ Protocol	PELCOP,PELCOD,LILIN,MINKING,NEON,STAR,VIDO,DSCP,VISCA,SAMSUNG, RM110,HY
	PTZ Control	pan, tilt, zoom, preset, cruise, trace
<b>Network</b>	Ethernet	10/100 Mbps Ethernet (RJ-45)
	Protocol	TCP/IP, DHCP, DDNS, NTP, SMTP
	Remote Control	-
<b>Others</b>	Power Supply	DC12V
	Operating Temperature	0°C ~50°C
	Humidity	10% ~ 90% Humidity
	Dimension	11.75"(L)×10"(W)×2.25"(H)

## Front/Back View



