

Husky

1080p Wi-Fi + PoE Outdoor Bullet Cloud Camera



Introduction

EZVIZ products have been designed for your entertainment, communication and security. When you install the EZVIZ APP on your smartphone or tablet, EZVIZ devices will connect to the cloud via their QR code. With EZVIZ Husky you can keep an eye on your home and surroundings.

Main Features



Full HD 1080p



Local video storage on a microSD/SDHC memory card up to 128GB



Wi-Fi Certified 2.4GHz



Dustproof and Waterproof



Night Vision, up to 100feet



Secure cloud recording* (Optional)

*Subscription is required for cloud recording.

Dimensions



Specifications

Model	CS-CV210 1080P Wi-Fi + PoE Outdoor Bullet Cloud Camera
Camera	
Image sensor	1/2.7" Progressive Scan CMOS
Minimum Illumination	0.02Lux @ (F2.2, AGC ON) , 0 Lux with IR
Shutter	1/30s to 1/100,000s
Lens	4mm @ F2.2 Horizontal View Angle: 90°, Diagonal View Angle: 107.5°
Lens Mount	M12
Day & Night	IR cut filter
DNR	3D DNR
IR Range	Up to 100 feet (30m)
WDR	HDR, Max. 120db
Compression	
Video Compression	H.264 Main Profile
Video Bit Rate	Hi-Def, Standard, and Basic . Adaptive bit rate.
Audio Bit Rate	Adaptive bit rate
Image	
Max. Resolution	1920 x 1080
Frame Rate	Up to 30fps, Adaptive
Network	
Storage	Support microSD card (≤ 128 GB)
Smart Alarm	Smart motion detection
One-key configuration	SmartConfig (Wi-Fi one-key configuration)
Interface Protocol	EZVIZ Cloud Proprietary Protocol
General Function	Dual-stream, Mirror image
Network Interface	1*RJ45 10M/100M Self-Adaptive Ethernet Port
Wireless parameters	
Standard	IEEE802.11b, 802.11g, 802.11n
Frequency Range	2.4 GHz to 2.4835 GHz
Channel Bandwidth	Support 20MHz
Security	64/128-bit WEP, WPA/WPA2, WPA-PSK/WPA2-PSK
Transmission Rate	802.11b: 11Mbps, 802.11g: 54Mbps, 802.11n: 150Mbps
General	
Operating Conditions	-22°F to 140 °F (-30°C ~ 60°C), Humidity 95% or less (non-condensing)
Power Consumption	12VDC ± 10%, 6W Maximum/Support PoE (802.3af)
Dimensions (inch)	6.81*3.28*2.75"(173mm*83.5mm*69.8mm)
Weight	0.73 lb (331 g)