





DEFENDERTM SECURITY



Specifications: 82-22140

Image Sensor	1/2.9" SONY 2.4MP CMOS Sensor (IMX323+NVP2441H)
Effective Picture Elements (H×V)	1080P , 1920*1080
Minimum Illumination	0.001 Lux/F1.2
S/N Ratio	≥50dB
Video Output	AHD/CVI/TVI/CVBS
Lens	Optional
Infrared LED	NO
Infrared Distance	NO
Auto Iris Support	YES
Day/Night	Auto (ICR) / Color / B&W
White Balance	Auto/Manual
Gain Control	Auto
Noise Reduction	3D NR
OSD Functions	Super DWDR, DEFOG, Sense-up, UTC
Housing	Metal
IR Cut Filter	YES
Operation Temperature	-10℃ ~ +50℃ RH95% Max
Storage Temperature	-20℃ ~ +60℃ RH95% Max
Power Source	DC12V(+/-10%)/300mA
Dimension	148(W) x 79(H) x 57(D)
Weight	585g