



Product Search

- [Product Solutions](#)
- [Corporate](#)
- [Support](#)
- [Where to Buy](#)
- [Press Room](#)
- [Partners](#)
- [Community](#)

Compact Wireless-N USB Adapter

GWU625



WHERE TO BUY

MSRP: \$24.95 USD

8 Like
0 Tweet

GEAR POWER™

Compare & Select

- Display All
- Description
- Features
- Function Diagram
- Requirements
- Package Contents
- Specifications
- Support

UPC: 881317507600

Function	GWU625
Power Consumption	Transmit : < 380mA. ; Receive: < 250mA.
Operating Temperature	0 ~ 50 celsius
Storage Temperature	-10 ~ 70 celsius
USB Specification	USB 2.0
Humidity	5 ~ 90% (non-condensing)
Transmission Power	17 dBm
Frequency Band	2.4GHz ~ 2.483GHz unlicensed ISM band
Modulation	IEEE 802.11n: BPSK, QPSK, 16-QAM, 64-QAM
Data Rate	IEEE 802.11n : 6, 9, 12, 18, 24, 36, 48, 54, 60, 90, 120, 180, 240, 270 and up to 300Mbps
Interface	USB 2.0
Security	64-bit or 128-bit WEP/WPA TKIP
Management	Windows-based Utility
Operating Range	100 - 400m, depending on surrounding environment
Encryption	64 bit / 128 bit WEP, TKIP, AES
Antenna Type	On board chip antenna
Range	Up to 320 ft
Chipset	RTL8191SU

Dimensions	GWU625
POP Information	
10" Peg Hook	7
6" Peg Hook	4
Unit Dimensions	
Height	53mm

Depth	8mm
Length	25mm
Inner Pack	
Width	137mm
Height	133mm
Depth	285mm
Inner Pack Qty.	6
Unit Package Dimensions	
Width	125mm
Height	165mm
Depth	37mm
Master Carton	
Width	150mm
Height	290mm
Depth	285mm
Master Carton Qty.	12
Weight	
Master Carton Wt.	1.44kg
Inner Pack Wt.	.6kg
Unit Pack Wt.	.08kg
Unit Wt.	8.54grams

14k

126

Follow [@iogear](#)

Follow [@IOGEARDeals](#)

[Click Here](#) to receive the IOGEAR Newsletter and / or Discounts

Like

G+1

Stay Connected

- [Facebook](#)
- [Twitter - IOGEAR News](#)
- [Twitter - IOGEAR Deals](#)
- [Youtube](#)
- [RSS Feed](#)
- [LTCM Communicator](#)
- [Blog](#)
- [Monthly Newsletter](#)
- [Bargain of the Week](#)

Hot Products

- [Media Hub / Travel Router](#)
- [Wireless HDMI](#)
- [iPhone Battery Packs](#)
- [Travel Router](#)

Popular Solutions

- [HDMI Switch](#)
- [KVM](#)
- [KVM DVI](#)
- [KVM Switch](#)
- [LCD KVM](#)
- [Mobile Accessories](#)
- [PC to TV](#)
- [Rackmount KVM](#)
- [USB Switch](#)
- [Video Splitter](#)
- [Video Switch](#)
- [Wireless Audio Video](#)
- [Internet on TV](#)
- [USB 3.0](#)
- [Secure KVM](#)
- [Wireless Video](#)
- [HDMI Extender](#)

Product Categories

- [A/V & Digital Home](#)
 - [Computer Accessories](#)
 - [KVM & KVMP](#)
 - [Mobility](#)
 - [Networking](#)
 - [Pro Audio & Video \(AVIOR\)](#)
- Landing Pages**
- [Wireless HDMI Matrix PRO](#)
 - [KeyMander](#)
 - [TuneTap](#)
 - [Shair Family Products](#)
 - [GearPower Chargers](#)

Company

- [About Us](#)
- [Green Initiative](#)
- [Mission Statement](#)
- [RoHS & WEEE Statement](#)
- [Privacy Statement](#)
- [Contact Us](#)
- [Webinars](#)

Support

- [Customer Support](#)
- [Knowledgebase](#)
- [Drivers & Manuals](#)
- [Product Registration](#)

Press & Media

- [Press Releases](#)
- [Press Kit](#)
- [Upcoming Events](#)
- [NewsFlash](#)
- [IOGEAR in the News](#)
- [Awards](#)
- [Hi-res Images](#)
- [Media Contact](#)

Where to Buy

- [IOGEAR eStore](#)
- [IOGEAR in Stores](#)
- [IOGEAR Distributors](#)