

## 2-Port USB 2.0 Automatic Printer Switch

GUB231



- Automatically\* switch from one computer to another when connecting to a USB printer or multi-function printer
- Simply press a button to switch a USB device between computers - No software installation required
- Active-port LED lights indicate which computer has access to the USB device
- Switch-lock function prevents other users from switching the USB device and ensures data access consistency
- USB 2.0 support with data transfer rate up to 480Mbps and USB 1.1 backward compatible
- No external power supply needed

IOGEAR's USB 2.0 Automatic Printer Switch allows two PCs and / or Macs to share one printer or multi-function printer. Simply submit a print job and the printer automatically\* switches to the preferred computer. The switch also enables two computers to easily share one external hard drive, scanner, or any USB device. No more plugging and unplugging between computers.


\* Automatic switch function is software based and only available with USB printer or the printer function of a multi-function printer. For connecting and using other types of USB devices, you can switch by using the push-button on the USB switch or with the included software.



## 2-Port USB 2.0 Automatic Printer Switch

### How does it work?

- Connect your USB device (i.e. printer, external hard drive, or scanner) to the USB-A connector
- Connect your computers (PC or Mac) to the USB-B connector
- Simply push the button to swap or enable automatic\* switch between two computers



### Requirements:

- Windows XP, Windows Vista 32-/64-bit, Windows 7 32-/64-bit
- Mac OS X v10.3.5 or later
- Available USB port (USB 2.0 port for High-Speed mode)

### Package Contents:

- 1 x USB 2.0 Auto Switch
- 1 x 6 ft. USB A-B Cable
- 1 x User Manual
- 1 x Application CD
- 1 x Registration / Warranty Card

### SPECIFICATIONS

Function	
Computer Connections	
Direct	USB Type B to Type A
Connectors	
Console	1 x USB Type A
Device Side	2 x USB Type B
Environment	
Humidity	0-80% RH
Operation Temperature	41 to 104 degree Fahrenheit
Storage Temperature	-4 to 140 degree Fahrenheit
LEDs	
Port Status	Green - Online / Orange - Locked
Host Status	Orange - Online
Operating System Support	Windows XP and above; Mac: 10.4.5, 10.5 and above
Power Consumption	DC 5V, 2.5W
Power Supply	USB Bus powered

Dimensions	
POP Information	
10" Peg Hook	4
6" Peg Hook	3
Unit Dimensions	
Width	2.5"
Height	2.75"
Depth	1"
Unit Package Dimensions	
Width	6"
Height	7.25"
Depth	2.25"
Master Carton	
Width	8"
Height	7"
Depth	15"
Master Carton Qty.	6
Weight	
Master Carton Wt.	4.5 lb.
Unit Pack Wt.	0.65 lb.
Unit Wt.	0.1 lb.