


Allgemeintoleranzen ISO 2768-m	Werkstoff -	Massstab: 2:1 (A3)	Gezeichnet	Datum	Name
			Freigegeben	29.03.05	jutz b
Zeichnung urheberrechtlich geschuetzt (DIN 34) (C)	-	-	Geändert	-	-
			Aend.-Nr.	-	Aend.-Index
Benennung RX-Serie NC3FRX			Ersatz fuer:	Blatt 1 von 2 Bl.	
NEUTRIK AG FL-9494 SCHAAN			Zeichn. Nr.	ST-NC3FRX	

XLR Cable Connector

NC*FRX & NC*MRX


Assembly Instructions



- (A)** Slide the boot onto the cable.
- (B)** Prepare cable as shown.
- (C)** Insert wires into the terminals and solder them.
- (D)** Slide insert into the housing until it snaps in.
Align insert with housing.
- (E)** Position the cable.
- (F)** Slide the chuck into the housing.
Pay attention to position chuck as shown.
- (G)** Position the cover.
Before place the cover choose the orientation of cable outlet by turning housing.
- (H)** Finish the installation by turning the bushing onto the connector.

Disassembly of the insert

- (I)** Remove cover and chuck.
- (J)** Push latch and turn housing approx. a half turn until housing can be separated.
- (K)** Lift the locking clip by help of a screw driver.
- (L)** Remove insert.



NEUTRIK AG
NEUTRIK Zürich AG
NEUTRIK USA Inc.
NEUTRIK (UK) Ltd.

LI T: +423 / 237 24 24 F: +423 / 232 53 93
CH T: +41 44 / 736 5010 F: +41 44 / 736 5011
USA T: +1 732 / 901 9488 F: +1 732 / 901 9608
UK T: +44 1983 / 811 441 F: +44 1983 / 811 439

NEUTRIK Vertriebs GmbH DE/NL/AT T: +49 8131 / 280 890 F: +49 8131 / 280 830
NEUTRIK France FR T: +33 1 / 4131 6750 F: +33 1 / 4131 0511
NEUTRIK Tokyo Ltd. JP T: +81 3 / 3663 4733 F: +81 3 / 3663 4796
NEUTRIK Hong Kong Ltd. HK T: +852 / 2687 6055 F: +852 / 2687 6052

www.neutrik.com



NEUTRIK
CONNECTING THE WORLD