



PRODUCT FACT SHEET

STREAMLIGHT JR.® LED FLASHLIGHT

MARKET APPLICATIONS: Premium Professional Light - Law Enforcement, Fire & Rescue, Automotive, Industrial, Outdoor, Consumer

DESCRIPTION: Ultra-compact, lightweight flashlight features the latest in power LED technology. New C4 premium LED technology produces 2 to 3 times the output of previous LEDs. Packaged with a black nylon flapless holster.

CASE MATERIAL: Machined aircraft aluminum with anodized finish; shock and water resistant. Available in black.

DIMENSIONS: Length: 6.5 in. (16.51 cm) Diameter: Major Diameter: 1.00 in. (2.54 cm)
Body Diameter: 0.73 in. (1.85 cm)

WEIGHT: 3.80 oz (107 grams)*

LENS: Unbreakable polycarbonate lens.

LIGHT SOURCE: Next generation C4 LED technology, impervious to shock with a 50,000 hour lifetime.


LIGHT OUTPUT: Up to 1,600 candela peak central intensity and 55 lumens measured system output. Textured parabolic reflector produces an even, wide beam hotspot.

ON/OFF: Push button tailcap - steady on and momentary on/off operation.

RUN TIME: Up to 4 hours of runtime to the 10% output level.

FEATURES: Internal Reflection Optics, "O" Ring Sealed, water resistant design, Maximum brightness throughout battery life.


BATTERY: Two (2) "AA" alkaline batteries; included in packaging

APPROVALS: Most models meet applicable European Community Directives. 

WARRANTY: Limited lifetime warranty.

OPTIONAL ACCESSORIES: Helmet clamp, Clip holder

* With batteries (included with purchase).



Made In China.