




# C-0150 Enclosure (50"x14")

Structured wiring enclosures from Channel Vision Technology are designed to be the central “brain” of the home sending signals to every room, with distribution from cable TV, satellite, speakers, IR, fiber optics, telephone, automation, internet, security cameras, and much more. The modular layout of these sturdy cabinets allow easy access and is upgradeable. Plus, with sizes of 12”, 19”, 28”, 38”, and 50” Channel Vision has an enclosure to fit any need.

**C-0150E (enclosure):**

- UL approved
- Modular push and lock product components
- Electrical gang box knockout with grounding screw
- Sturdy 16 gauge steel construction
- Powder coated white paint
- Includes wire management straps, large cable knockouts, grommets, cable identifiers, and cardboard rough-in cable protector

C-0150E and C-0150HC  
 (sold separately)



**C-0150HC (cover):**

- Oversized hinged cover with louvered vents

**Specifications:**

<b>Dimensions:</b>	50”(L) x 14”(W) x 3 5/8”(D)	<b>Electrical Knockout size</b>	Single Gang
<b>Material:</b>	C.R.S	<b>Knockout-Top</b>	5
<b>Gauge:</b>	16 awg	<b>Knockout Box</b>	3
<b>Indoor/Outdoor:</b>	Indoor Use	<b>Knockout Side</b>	1 on each side
<b>Knockout size:</b>	1 3/4”	<b>Universal Mounting Modules</b>	

**Optional Snap-In Modules and Accessories:**

C-0202 Passive Splitter 1 In 2 Out	C-0434 Panasonic KSU Distribution	C-1102 Satellite Diplexer 1 In 8 Out
C-0204 Passive Splitter 1 In 4 Out	C-0436 4 Line 8 Out Telephone Distribution RJ45	C-1114 HDTV 5x8 Out Multi Switch Amplified
C-0208 Passive Splitter 1 In 8 Out	C-0441 110 Telecom Module w/ 100 Pair Capacity	C-1115 HDTV Cascade System AMP
C-0213 Bracket, “F” Barrel Connecting Termination	C-0501 Network Hub Distribution 110 Cat5E	C-1116 HDTV 8 Out Cascade Multi Switch
C-0214 Basic Service Module (4RF, 6 TELE)	C-0514 4 Port Router with Firewall	C-1117 HDTV 6 Out Cascade Multi Switch
C-0215 Home Office Module (RF, TELE, DATA)	C-0510 5 Port Switch, 10/100 Mbps	C-1118 HDTV 4 Out Cascade Multi Switch
C-0216 Basic Service Module	C-0518 8 Port Switch, 10/100 Mbps	C-1134 3 In 4 Out Amplified Multiswitch
C-0301 Mini-Series Modulators	C-0601 Fiber Optics Termination Bracket	C-1158 5 In 8 Out Amplified Multiswitch
C-0302 2 Input Modulator E-Series	C-0622 Fiber Optics Spool Plate w/ Lid	C-1201 IR Distribution (8 In 1 Out)
C-0303 3 Input Modulator E-Series	C-0702 Power Strip 6 Outlets	C-1305 12” Plexi Lid
C-0304 4 Input Modulator E-Series	C-0703 Power Distribution-Low Voltage 12VDC	C-1306 19” Plexi Lid
C-0308 12” x 5-1/2” Horizontal Mounting Plate	C-0901 Home Automation I/O Board & Controller	C-1307 38” Plexi Lid
C-0309 6” x 9” Vertical Mounting Plate	C-0902 TE 200 Telephone Intercom	C-1308 50” Plexi Lid
C-0310 10 dB Amplifier (DC/IR Passing)	C-0903 Automation Voice & Telephone Module	IR-1001 IR Connect Block – Amp-Regulated
C-0314 1 In 4 Out 8dB Amplifier (DC/IR Passing)	C-0904 Automation LCD Panel	IR-2001 J-Box Repeater
C-0315 15 dBmV Bi-directional Amplifier	C-0905 Automation Interface to PC & Software	IR-2200 IR Tube Repeater, 1/2”
C-0329 2 In 8 Out Amplified Splitter/Combiner	C-0906 Wireless Emergency Alert Transmitter/Rec.	IR-3002 IR Dual Flasher w/ common LED
C-0332 1 in 16 out RF Amplifier	C-0907 Computer Software for C-0901	Xan-CPL94B RF/IR Coupler
C-0408 RJ45 Interconnect 1’ Cat5E	C-1001 Speaker Distribution	Xan-INJ94 RF/IR Injector
C-0409 RJ45 Interconnect 3’ Cat5E		SW-1302 Snap pin, fastens brackets to chassis
C-0432 4 Line 8 Out Telephone Distribution 110		

