

DS-2CE16D1T-IR



Key Features

- 2 Megapixel high-performance CMOS
- Turbo HD output, up to 1080P resolution
- True Day/Night, Smart IR
- Up to 20m IR distance
- IP66 weatherproof
- OSD menu controlled via UTC

Specification

Model	DS-2CE16D1T-IR
Parameter	Turbo HD1080p IR Bullet Camera
Camera	
Image Sensor	Progressive Scan CMOS
Signal System	PAL/NTSC
Effective Pixels	1930(H)*1088(V)
Min. Illumination	0.01 Lux @(F1.2,AGC ON), 0 lux with IR
Shutter Time	1/25(1/30) s to 1/50,000 s
Lens	2.8mm, 3.6mm, 6mm optional
	Angle of View: 105.8°(2.8mm), 84.3°(3.6mm), 55.4°(6mm)
Lens Mount	M12
Angle Adjustment	Pan: 0 - 360°, Tilt: 0 - 90°, Rotation: 0 - 360°
Day & Night	ICR
Synchronization	Internal synchronization
Video Frame Rate	1080p@25fps/1080p@30fps
HD Video Output	1 turbo HD output
S/N Ratio	More than 52dB
Menu	

AGC	Support
D/N Mode	Color/BW/EXT
White Balance	Auto/Manual
BLC	Support
Language	English/Chinese
Functions	Digital noise reduction, Mirror
General	
Working Temperature/Humidity	-40 °C - 60 °C (-40 °F - 140 °F) Humidity 90% or less (non-condensing)
Power Supply	12V DC
Power Consumption	Max. 3W
Weather Proof Ratings	IP66
IR Range	Up to 20m
Communication	Up the coax Protocol: HIKVISION-C(Coaxitron)
Dimension	Φ70×149.5mm (Φ2.76"×5.89")
Weight	290 g (0.64 lb)

Order Model

DS-2CE16D1T-IR

Dimension

