

SP111-31-C301

Part Number: NX.GMBEK.001

Processor & Chipset

Processor Manufacturer

Intel®

Processor Type

Celeron®

Processor Model

N3350

Processor Speed

1.10 GHz

Burst Frequency

2.40 GHz

Processor Core

Dual-core (2 Core™)

Cache

2 MB

64-bit Processing

Yes

Hyper-Threading

No

Memory

Standard Memory

4 GB

Maximum Memory

8 GB

Memory Technology

DDR3L SDRAM

Number of Total Memory Slots

1

Memory Card Reader

No

Storage

Flash Memory Capacity

32 GB

Optical Drive Type

No

Display & Graphics

Screen Size

29.5 cm (11.6")

Display Screen Type

Active Matrix TFT Colour LCD

Display Screen Technology

In-plane Switching (IPS) Technology

Aspect Ratio

16:9

Screen Mode

Full HD

Screen Resolution

1920 x 1080

Backlight Technology

LED

Touchscreen

Yes

Multi-touch Screen

Yes

HDCP Supported

Yes

Graphics Controller Manufacturer

Intel®

Graphics Controller Model

HD Graphics 500

Graphics Memory Technology

DDR3L SDRAM

Graphics Memory Accessibility

Shared

TV Card

No

Network & Communication

Wireless LAN

Yes

Wireless LAN Standard

IEEE 802.11ac

Bluetooth

Yes

Built-in Devices

Front Camera/Webcam

Yes

Front Camera/Webcam Video Resolution

1280 x 720

Microphone

Yes

Finger Print Reader

No

Speakers

Yes

Number of Speakers

2

Sound Mode

Stereo

Sensor Type

Accelerometer

Interfaces/Ports

HDMI

Yes

Total Number of USB Ports

3

Number of USB 2.0 Ports

2

Number of USB 3.0 Ports

1

Audio Line Out

Yes

Software

Operating System Platform

Windows

Operating System

Windows 10 Home

Operating System Architecture

64-bit

Input Devices

Keyboard

Yes

Pointing Device Type

TouchPad

TouchPad Features

Multi-touch Gesture

Battery Information

Number of Cells

4-cell

Battery Chemistry

Lithium Ion (Li-Ion)

Battery Capacity

3220 mAh

Battery Energy

48 Wh

Maximum Battery Run Time

9 Hour

Power Description

Maximum Power Supply Wattage

45 W

Physical Characteristics

Colour

Obsidian Black

Height (Front)

20.30 mm

Height (Rear)

20.30 mm

Height

20.3 mm

Width

298 mm

Depth

210 mm

Weight (Approximate)

1.50 kg

Miscellaneous

Package Contents

Spin SP111-31-C301 Notebook

Lithium Ion Battery

AC Adapter

Security Features

BIOS Passwords :

User

Supervisor

HDD