

DYMO®

MobileLabeler™

Easy labelling with your smartphone



Features:

- Bluetooth® connectivity allows for quick, seamless setup with a smartphone or tablet
- Free DYMO® Connect mobile app works with iOS® or Android™ smartphones for an intuitive labelling experience
- Design labels using borders, styles and popular Google® and Apple® font libraries
- DYMO® Connect features spellcheck and voice-to-text to help reduce errors and save time
- Includes rechargeable battery - no AA batteries required
- Prints labels from 6 mm up to 24 mm wide in a variety of colours



Connect. Create. Print.

DYMO® Connect:

Compatibility

- Android™ 4.4 or later
- iOS® 8.0 or later



 **Bluetooth®** For easy, wireless connectivity.



Easy Peel



UV Resistant



Water Resistant



Temperature

Standard Label:
-18°C to 90°C

Durable Label:
-40°C to 80°C

MobileLabeler Specifications

Item #1978247 RRP £ 121.67

MobileLabeler Pack Contents

DYMO® MobileLabeler
D1 Starter Label Cassette (24 mm x 3 m black on white)
USB Cable
Rechargeable Lithium Ion Battery
AC Adapter
Quick Start Guide

MobileLabeler Pack Unit

Length	12.3 cm
Width	21 cm
Height	20.5 cm
Weight (kg)	1.42
Shipper	
Length	42.5 cm
Width	22.5 cm
Height	39.5 cm
Weight (kg)	9.2
Units per Shipper	6



D1 Labels

Recommended Applications



- Files and Folders
- Binders
- Office Organisation
- Office Supplies
- Asset Tracking
- IT Equipment
- Kitchen Appliances
- Product Samples
- Closet Organisation
- Garage Organisation

D1 labels for the MobileLabeler



D1 Standard (Available in 6 mm, 9 mm, 12 mm, 19 mm, 24 mm)

	BLACK•WHITE	RED•WHITE	BLACK•YELLOW	BLACK•RED	BLACK•CLEAR	RED•CLEAR
6 mm	S0720780	-	S0720790	-	S0720770	-
9 mm	S0720680	S0720700	S0720730	S0720720	S0720670	-
12 mm	S0720530	S0720550	S0720580	S0720570	S0720500	S0720520
19 mm	S0720830	S0720850	S0720880	S0720870	S0720820	-
24 mm	S0720930	-	S0720980	S0720970	S0720920	-

	BLUE•WHITE	WHITE•BLACK	BLACK•BLUE	BLACK•GREEN	WHITE•CLEAR	BLUE CLEAR
6 mm	-	-	-	-	-	-
9 mm	S0720690	-	S0720710	S0720740	-	-
12 mm	S0720540	S0720610	S0720560	S0720590	S0720600	S0720510
19 mm	S0720840	S0720910	S0720860	S0720890	S0720900	-
24 mm	S0720940	S0721010	S0720960	S0720990	S0721000	-

D1 Durable (Available in 12 mm)

	BLACK•WHITE	WHITE•RED	WHITE•BLACK	BLACK•ORANGE
12 mm	1978364	1978366	1978365	1978367

DYMO and the DYMO logo are trademarks or registered trademarks of Sanford, L.P. or its affiliates. All other trademarks are the property of their respective owners.

