

Sunset Vintage Globe 80mm 5W (40W) 1800K 380lm B22 Dimmable Lamp*Partcode: ILGLOBB22D008 / Page: 1***Globe 80mm**

Create a relaxing ambience with an ultra-warm (1800K), dimmable, energy-saving LED filament lamp. The Sunset range has a retro look with tinted amber glass and an eye-catching vintage design.

Built using the latest LED filament technology to deliver an A+ energy rating and 93% energy savings compared to the incandescent lamp it replaces. Enjoy the classic aesthetic look but with an improved lifetime of 15,000 hours.

Product Details

Partcode: ILGLOBB22D008

Check Code: 729262

Range Name: Sunset

Product Type: Vintage Decorative

Warranty: 2 Years

CE / RoHS: Yes

Physical Data

Lamp Base: B22

Base Type: Bayonet cap

Globe Type: Globe 80

Globe Finish: Clear

Material: Aluminium, Glass

Construction: Glass shell, filament strip, Aluminium Base

Physical Data

Length: 120mm
Width: 80mm
Diameter: 80mm
Weight (Unpackaged Single Unit): 130g
Lamp or Luminaire Shape: Round
Lamp Fixing: Pendant, Chandelier, Wall


Electrical Data

Voltage Range: 220-240V
Power Consumption: 5.0 Watts
Driver included: Yes
Electric Current: AC
Ampage: 29.00mA
Frequency Range: 50/60 Hz
Power Factor: ≥ 0.70
Wattage Equivalent: 33 Watts
Dimming: Dimmable
LVD Certified: Yes
EN: EN-62560

Light Data

Lumens: 380lm
Lumens per Watt: 76.0lm/W
Beam Angle: 290°
Correlated Colour Temperature (CCT): 1,800k
Colour Rendering Index (CRI): ≥ 78
LED Type: Filament chip
Instant on - Less than 1 second: Yes
Lifetime: 15,000 hrs
Switching Cycles: $>7,500 X$

Environmental



Energy Rating: A+

Lowest Operating Temperature: -20 degrees

Maximum Operating Temperature: 45 degrees

IP (Ingress Protection) Rating: IP20

Hg 0% (Mercury Free): Yes

Packaging



EAN Barcode (unit of 1): 5055788224099

Packaged Weight (Unit of 1): 140g

Length (unit of 1): 86mm

Width (unit of 1): 86mm

Depth (unit of 1): 134mm

Outer packaging info available on website

Product data last updated on: Monday, August 7, 2017 - 14:37