

Hard Disk Model	TOSHIBA MK5055GSX
Disk Family	MK-5055GSX
Form Factor	2.5"
Capacity	500 GB (500 x 1 000 000 000 bytes)
Number Of Disks	2
Number Of Heads	4
Rotational Speed	5400 RPM
Rotation Time	11.11 ms
Average Rotational Latency	5.56 ms
Disk Interface	Serial-ATA/300
Buffer-Host Max. Rate	300 MB/seconds
Buffer Size	8192 KB
Width	69.85 mm (2.75 inch)
Depth	100 mm (3.94 inch)
Height	9.5 mm (0.37 inch)
Weight	102 grams (0.22 pounds)
Required Power For Spinup	940 mA
Power Required (Seek)	2.7 W
Power Required (Idle)	1.0 W
Power Required (Standby)	0.25 W
Manufacturer	Toshiba Corp., Storage Device Division