

Basic

Brand Name: Acer
DVI: Yes
Environmentally Friendly: Yes
Graphics Controller: Intel
Manufacturer:
Graphics Controller Model: HD Graphics 530
Graphics Memory Accessibility: Shared
Graphics Memory Technology: DDR4 SDRAM
Number of USB 2.0 Ports: 4
Operating System Architecture: 64-bit
Operating System Platform: Windows
Operating System: Windows 10 Pro
Optical Drive Type: DVD-Writer
Processor Manufacturer: Intel
Processor Model: i3-6100
Processor Speed: 3.70 GHz
Processor Type: Core i3
Product Family: Extensa M2710
Product Type: Desktop Computer
Standard Memory: 4 GB
Total Hard Drive Capacity: 1 TB
Total Number of USB Ports: 6
VGA: Yes

Display & Graphics

Graphics Controller: Intel
Manufacturer:
Graphics Controller Model: HD Graphics 530
Graphics Memory Accessibility: Shared
Graphics Memory Technology: DDR4 SDRAM
TV Card: No

General Information

Brand Name: Acer
Manufacturer Part Number: DT.X0TEK.008
Manufacturer Website Address: <http://www.acer.co.uk>
Manufacturer: Acer, Inc
Product Line: Extensa
Product Name: Extensa M2710 Desktop Computer
Product Series: M2710
Product Type: Desktop Computer

I/O Expansions

Number of M.2 Interfaces: 1
Number of PCI Express x1 Slots: 1
Number of PCI Express x16 Slots: 1
Number of Total Expansion Slots: 2

Input Devices

Keyboard Type: Physical Keyboard
Keyboard: Yes
Pointing Device Type: Mouse

Interfaces/Ports

Audio Line In: Yes
Audio Line Out: Yes
DVI: Yes
Modem (RJ-11): No
Network (RJ-45): Yes
Number of USB 2.0 Ports: 4
Number of USB 3.1 Gen 1 Ports: 2
Total Number of USB Ports: 6
VGA: Yes

Memory

Maximum Memory: 16 GB
Memory Card Reader: No
Memory Standard: DDR4-2133/PC4-17000
Memory Technology: DDR4 SDRAM

Standard Memory: 4 GB

Miscellaneous

Certifications & Standards:

- DMI
- PC2001
- BSMI
- CB
- CE
- FCC

Environmental Certification: RoHS
Environmentally Friendly: Yes
Features: Security Slot
Package Contents:

- Extensa M2710 Desktop Computer
- USB Keyboard
- USB Mouse

Network & Communication

Ethernet Technology: Gigabit Ethernet
Modem: No

Physical Characteristics

Depth: 372 mm
Height: 365 mm
Width: 175 mm

Power Description

Maximum Power Supply Wattage: 220 W

Processor & Chipset

64-bit Processing: Yes
Cache: 3 MB
Chipset Manufacturer: Intel
Chipset Model: H110 Express
Direct Media Interface: 8 GT/s
Hyper-Threading: Yes
Number of Processors Installed: 1
Number of Processors Supported: 1
Processor Core: Dual-core (2 Core)
Processor Generation: 6th Gen
Processor Manufacturer: Intel
Processor Model: i3-6100
Processor Speed: 3.70 GHz
Processor Type: Core i3
vPro Technology: No

Software

Operating System Architecture: 64-bit
Operating System Platform: Windows
Operating System: Windows 10 Pro

Storage

Hard Drive Configuration: 1 x 1 TB
Hard Drive Interface: Serial ATA/300
Hard Drive RPM: 7200
Number of Hard Drives: 1
Optical Drive Type: DVD-Writer
Optical Media Supported: DVD±R/±RW
Total Hard Drive Capacity: 1 TB