

The robust all-rounder for any applications – always ready when, and where you need light!

Rechargeable LED work floodlight 10W

Technical highlights

- Flexibly usable, rechargeable work floodlight for indoor and outdoor use, IP54.
- Bright working light at any time, also at locations without power connection.
- Integrated lithium-ion battery, charging duration about 4.75 hours.
- With integrated overcharging / total discharge protection and battery condition display.
- With On/off switch, adjustable in 2 different brightness levels (50%/100%).
- Powerbank function: USB charging connection 1A for devices with USB charging cable such as smart phones, MP3 players, navigation units, etc.
- Charging via micro USB connection (5V, 1A), USB charging cable included.
- Housing made of massive die-cast aluminium, edge protection of high-quality plastic.
- Impact- and fall-protected from heights up to 2 m.
- Stable, multi-step, foldable frame for positioning.
- With high-quality bag for safe transport.



Technical data

Power consumption:	10W
Luminous flux:	max. 1000lm
IP class:	IP54
Colour temperature:	6500K
Life cycle LED:	50000h
Radiation angle:	ca. 110°
Protection class:	III
Rechargeable battery:	Lithium-ion 3.7 V / 4400 mAh
Charging duration:	ca. 4.75 h (with max. charging current 1 A)
Lighting duration:	3h (100%), 6h (50%)
USB output:	5V, max. 1A
Charging input:	Micro USB, 5V 1A
Temperature range:	-10°C - +40°C
Dimensions:	12.3 x 17.0 x 4.3cm
Weight:	0.85 kg

Scope of delivery / art. No. / EAN no.

- Inc. USB charging cable and bag.
- Packed in a coloured sales cardboard box
- Type designation ML CA 110 M DE 4113
- Art. no. 1173080 / EAN 4007123646869

- PU: 1
- Available from August 2017

