

KFM LED

KFL026024

Old item no.: 18115LG



KFM LED T45 Lg 900 840 5D CLA NA

KFM LED produces nearly 75% greater light output than traditional KFM models. A heavy-duty, all-metal construction with sleek design, adjustable arm and excellent light output makes the KFM suitable for a variety of industrial applications. No knobs to tighten, nothing to adjust. A flexible, self-balancing shade and fully-enclosed, hands-free neck design combined with 45" heavy-duty internal-spring parallel, three-pivot K-arm, allows the lamp head to be secured in any position and are ideal for environments where FOD is a concern. The quality and positioning of the LEDs across two semi-circular modules allows for virtually shadow-free 5-diopter (2.25X) magnification and excellent color rendition. Edge clamp mount. Color: light grey.



Lightsource

Number of lamps	1
Lamp power (W)	11
Lightsource	LED
CRI and/or Color Temperature	80 CRI, 4000K
Lumen/Watt	82
Lumen Out	900

Optic

Primary Lens (D)	5
Working distance (mm)	200
Magnification (X)	2.25

Dimensions

Net weight (kg)	4,2
Arm length (in.)	45

Electrical data

Maximum frequency (Hz)	60
Minimum frequency (Hz)	50
Maximum voltage (V)	120
Voltage from (V)	100
Total consumption (W)	11

Technical data

Maximum ambient temperature (°C)	25
IP classification	20

Body

Body color	Grey
------------	------

Termination

Mounting	Edge clamp
----------	------------

KFM LED
KFL026024



KFM LED T45 Lg 900 840 5D CLA NA

KFM LED produces nearly 75% greater light output than traditional KFM models. A heavy-duty, all-metal construction with sleek design, adjustable arm and excellent light output makes the KFM suitable for a variety of industrial applications. No knobs to tighten, nothing to adjust. A flexible, self-balancing shade and fully-enclosed, hands-free



45" heavy-duty internal-spring parallel,



Drawings

