

IFM Magnifiers

16353LG

Old item no.: 16353LG



IFM2K 5D 3C LIGHT GRAY/GRIS

IFM is an ideal lighter-duty magnifier for low-power inspection. A 22W circline fluorescent lamp provides 360° shadow-free illumination and a lamp diffuser cover protects the bulb from damage. 5-diopter (2.25X) lens. 30" external spring-balanced arm. Weighted base. Color: light grey.



Lightsource

Number of lamps	1
Lamp power (W)	22
Lamp base	G10Q
CRI and/or Color Temperature	4100K
Lightsource	T9

Optic

Color of reflector	White
Working distance (mm)	200
Material of reflector	PC
Magnification (X)	2.25

Body

Body material	Steel
Body color	Grey

Electrical data

Maximum frequency (Hz)	60
Minimum frequency (Hz)	50
Maximum voltage (V)	120
Voltage from (V)	100

Dimensions

Net weight (kg)	0
Gross weight (lb.)	31
Arm length (in.)	30

Termination

Cord length (ft)	6
Mounting	Weighted base

Ballast

Type of Ballast	Electromagnetic
-----------------	-----------------