

KFM

# KFK025790

Old item no.: 17255LG



## KFM-2/FE 5D 3C Lg

KFM has a sturdy all-metal construction with a sleek design, flexible arm and excellent light output suitable for a variety of industrial, laboratory, cosmetology and low-vision applications. The flexibility of the neck assembly and patented internal spring 30" K-arm makes exact positioning easy. 5-diopter (2.25X) lens. Weighted base. Color: Light grey.



### Optic

Color of reflector	White
Material of diffuser	Polycarbonate
Primary Lens (D)	5
Working distance (mm)	200
Material of reflector	P C
Magnification (X)	2.25

### Electrical data

Maximum frequency (Hz)	60
Minimum frequency (Hz)	50
Maximum voltage (V)	120
Voltage from (V)	100

### Body

Body color	Grey
Body material	Aluminum

### Technical data

IP classification	20
-------------------	----

### Lightsource

Number of lamps	1
Lamp power (W)	22
Lamp base	G10Q
CRI and/or Color Temperature	4100K
Lightsource	T9

### Dimensions

Net weight (kg)	0
Arm length (in.)	30
Gross weight (lb.)	50

### Termination

Mounting	Table/desk base
Cord length (ft)	6

### Ballast

Type of Ballast	High frequency
-----------------	----------------