

KFM LED

# KFL026023

Old item no.: 18113BK



## KFM LED T45 BI 900 840 3D CLA NA

KFM LED produces nearly 75% greater light output than traditional KFM models. A heavy-duty, all-metal construction with sleek design, adjustable arm and excellent light output makes the KFM suitable for a variety of industrial applications. No knobs to tighten, nothing to adjust. A flexible, self-balancing shade and fully-enclosed, hands-free neck design combined with 45" heavy-duty internal-spring parallel, three-pivot K-arm, allows the lamp head to be secured in any position and are ideal for environments where FOD is a concern. The quality and positioning of the LEDs across two semi-circular modules allows for virtually shadow-free 3-diopter (1.75X) magnification and excellent color rendition. Edge clamp mount. Color: black.



### Lightsource

Number of lamps	1
Lamp power (W)	11
Lightsource	LED
CRI and/or Color Temperature	80 CRI, 4000K
Lumen/Watt	82
Lumen Out	900

### Optic

Primary Lens (D)	3
Magnification (X)	1.75
Working distance (mm)	330

### Dimensions

Net weight (kg)	3,9
Arm length (in.)	45

### Electrical data

Maximum frequency (Hz)	60
Minimum frequency (Hz)	50
Maximum voltage (V)	120
Voltage from (V)	100
Total consumption (W)	11

### Technical data

Maximum ambient temperature (°C)	25
IP classification	20

### Body

Body color	Black
------------	-------

### Termination

Mounting	Edge clamp
----------	------------

KFM LED  
KFL026023



KFM LED T45 BI 900 840 3D CLA NA

KFM LED produces nearly 75% greater light output than traditional KFM models. A heavy-duty, all-metal construction with sleek design, adjustable arm and excellent light output makes the KFM suitable for a variety of industrial applications. No knobs to tighten, nothing to adjust. A flexible, self-balancing shade and fully-enclosed, hands-free

IP20 LED cULm 45" heavy-duty internal-spring parallel,



Drawings

