

IFM Magnifiers

**16346LG**

Old item no.: 16346LG



IFM1A 5D 3C LIGHT GRAY/GRIS

IFM is an ideal lighter-duty magnifier for low-power inspection. A 22W circline fluorescent lamp provides 360° shadow-free illumination and a lamp diffuser cover protects the bulb from damage. 5-diopter (2.25X) lens. 45" external spring-balanced arm. Edge clamp mount. Color: light grey.



**Lightsource**

Number of lamps	1
Lamp power (W)	22
Lamp base	G10Q
CRI and/or Color Temperature	4100K
Lightsource	T9

**Optic**

Color of reflector	White
Working distance (mm)	200
Material of reflector	PC
Magnification (X)	2.25

**Body**

Body material	Steel
Body color	Grey

**Electrical data**

Maximum frequency (Hz)	60
Minimum frequency (Hz)	50
Maximum voltage (V)	120
Voltage from (V)	100

**Dimensions**

Net weight (kg)	0
Gross weight (lb.)	9
Arm length (in.)	45

**Termination**

Cord length (ft)	6
Mounting	Edge clamp

**Ballast**

Type of Ballast	Electromagnetic
-----------------	-----------------