

SAK Series
Q 3 AKZ4

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 1429-0
Fax: +49 5231 14292083
www.weidmueller.com



Klippon® Connect with clamping yoke Technology

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

General ordering data

| | |
|------------|---|
| Type | Q 3 AKZ4 |
| Order No. | 0336500000 |
| Version | SAK Series, Cross-connector, for cross-connection link, No. of poles: 3 |
| GTIN (EAN) | 4008190121730 |
| Qty. | 50 pc(s). |

SAK Series
Q 3 AKZ4

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 1429-0
 Fax: +49 5231 14292083
 www.weidmueller.com

Technical data**Dimensions and weights**

| | | | |
|------------|---------|-----------------|------------|
| Width | 17.2 mm | Width (inches) | 0.677 inch |
| Height | 4 mm | Height (inches) | 0.157 inch |
| Depth | 9.9 mm | Depth (inches) | 0.39 inch |
| Net weight | 2.328 g | | |

Material data

| | | | |
|----------|------|--------|------|
| Material | CuSn | Colour | Grey |
|----------|------|--------|------|

System specifications

| | | | |
|---------|---------------------------|---------------|------|
| Version | for cross-connection link | Mounting rail | none |
|---------|---------------------------|---------------|------|

Additional technical data

| | | | |
|--------------------------|---------|---------------------|-----------------|
| Explosion-tested version | No | Installation advice | Direct mounting |
| Type of fixing | Screwed | | |

Dimensions

| | |
|-----------------|--------|
| Pitch in mm (P) | 6.1 mm |
|-----------------|--------|

Rating data

| | |
|---------------|------|
| Rated current | 24 A |
|---------------|------|

Classifications

| | | | |
|------------|-------------|------------|-------------|
| ETIM 3.0 | EC000489 | ETIM 4.0 | EC000489 |
| ETIM 5.0 | EC000489 | ETIM 6.0 | EC000489 |
| UNSPSC | 30-21-18-01 | eClass 5.1 | 27-14-11-40 |
| eClass 6.2 | 27-14-11-40 | eClass 7.1 | 27-14-11-40 |
| eClass 8.1 | 27-14-11-40 | eClass 9.0 | 27-14-11-40 |
| eClass 9.1 | 27-14-11-40 | | |

Product information

| | |
|---------------------------------|---|
| Descriptive text technical data | Rated current is 32 A for all cross-connections when used in DK 4/DK4Q and QV versions. |
| Descriptive text accessories | Q2-Q10 AKZ 4, can also be used for all DK 4/DK4Q and DK4QV versions. |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|--------------------|--|
| Brochure/Catalogue | CAT 1 TERM 16/17 EN |
| Engineering Data | EPLAN, WSCAD, Zuken E3.S |