

**W-Series  
WQV 35/2**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 1429-0  
Fax: +49 5231 14292083  
www.weidmueller.com

**Klippon® Connect with clamping yoke Technology**

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

**General ordering data**

Type	WQV 35/2
Order No.	<a href="#">1053060000</a>
Version	W-Series, Cross-connector, For the terminals, No. of poles: 2
GTIN (EAN)	4008190097349
Qty.	50 pc(s).

**W-Series**  
**WQV 35/2**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 1429-0  
 Fax: +49 5231 14292083  
 www.weidmueller.com

**Technical data****Dimensions and weights**

Width	9.85 mm	Width (inches)	0.388 inch
Height	28 mm	Height (inches)	1.102 inch
Depth	28 mm	Depth (inches)	1.102 inch
Net weight	13.02 g		

**Temperatures**

Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C
----------------------------------	--------	----------------------------------	--------

**Material data**

Material	PA 66	Colour	Yellow
UL 94 flammability rating	V-2		

**System specifications**

Version	For the terminals	Mounting rail	none
---------	-------------------	---------------	------

**Additional technical data**

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	Screwed		

**Cross-connector**

No. of cross-connected terminals	2	Rated current, 2-pole	125 A
Rated current, multi-pole	135 A	Tightening torque range for fixing screw	1.2...2.4 Nm
Type	Cross-connector		

**Dimensions**

Pitch in mm (P)	16 mm	TS 35 offset	28 mm
-----------------	-------	--------------	-------

**Rating data**

Rated voltage	400 V	Rated current	138 A
---------------	-------	---------------	-------

**Classifications**

ETIM 3.0	EC000489	ETIM 4.0	EC000489
ETIM 5.0	EC000489	ETIM 6.0	EC000489
UNSPSC	30-21-18-01	eClass 5.1	27-14-11-40
eClass 6.2	27-14-11-40	eClass 7.1	27-14-11-40
eClass 8.1	27-14-11-40	eClass 9.0	27-14-11-40
eClass 9.1	27-14-11-40		

**Approvals**

ROHS	Conform
------	---------

**Data sheet****W-Series  
WQV 35/2**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 1429-0  
Fax: +49 5231 14292083  
www.weidmueller.com

**Technical data****Downloads**

---

Brochure/Catalogue	<a href="#">CAT 1 TERM 16/17 EN</a>
Engineering Data	<a href="#">EPLAN, WSCAD, Zuken E3.S</a>
Engineering Data	<a href="#">1053060000_09134_WQV_35-2_STP.stp</a>
User Documentation	<a href="#">Beipackzettel_WQV.pdf</a>

---