

## 02 02 225 T

### High Leverage Combination Pliers with tether attachment point



- 35 % less effort required than with conventional combination pliers
- With cutting edges (hardness approx. 63 HRC) for heavy duty
- Easier work due to optimised leverage
- Easier cutting, powerful gripping, bending and pulling
- Long cutting edges for thicker cables
- With gripping zones for flat and round material, suitable for versatile use
- High-grade special tool steel, forged, multi stage oil-hardened
- Pliers with tether attachment point for mounting a fall protection

<b>Article No.</b>	02 02 225 T
<b>EAN</b>	4003773079934
<b>Pliers</b>	black atramentized
<b>Head</b>	polished
<b>Handles</b>	with multi-component grips, with integrated tether attachment point for a tool tether
<b>Cutting capacities hard wire (diameter) Ø mm</b>	3,0
<b>Cutting capacities piano wire (diameter) Ø mm</b>	2,5
<b>Cutting capacity copper cable, multiple-stranded (diameter) Ø mm</b>	14,0
<b>Cutting capacity copper cable, multiple-stranded mm<sup>2</sup></b>	25,0
<b>Length mm</b>	225
<b>Net weight g</b>	401



*technical change and errors excepted*