



CCTVX CAMBF4 1MP HD Bullet Camera

SPECIFICATIONS

Model NO.	CAMBF4
Camera	
Image Sensor	OV9732
Main processor	Hi3518E
Resolution	1MP (720P)
Effective Pixels	1280 x 720
Compression	H.264/H.265/JPEG/AVI/MJPEG
TV System	PAL/NTSC
Electronic Shutter Time	Auto: PAL 1/25-1/10000Sec; NTSC 1/25-1/10000Sec
S/N Ratio	≥52dB
Scanning System	Progressive
SD Card	NO
Video Output	Network
LENS Type	
Focus Length	Board Lens 3.6mm/F2.0
Focus Control	Fixed
Lens Type	Fixed
Pixels	2MP
Night Vision	
Infrared LED	42μx 2PCS
Infrared Distance	30M
IR Status	Under 10 Lux By CDS
IR Power On	CDS Auto Control
Network	
Ethernet	RJ-45 (10/100Base-T)
Protocol	TCP/IP,ICMP,HTTP,HTTPS,FTP,DHCP,DNS,DDNS,RTP,RTSP,RTCP,NTP,SMTP
ONVIF	Support ONVIF 2.4
P2P	YES, Support QR Code
POE	Optional, Support IEEE 802.3af
WIFI	Supported.
Video Delay	0.3S (Within the Lan)
Main Stream 1	1280*720@(1-25)fps(default resolution:1280*720/frame rate:20fps/bit rate:1.5Mbps)
Main Stream 2	/
Main Stream 3	/
Sub Stream 1	720*480@(1-30)fps(1-30)fps(default frame rate:20fps/bit rate:0.5Mbps)
Sub Stream 2	/
Sub Stream 3	/
Tri Stream	
IE Brower	IE8-11, Google Chrome, Firefox, Safari, Mac Safari
Smart Phone	iPhone, iPad, Android, Android Pad
Camera Features	
Day/Night	Color/ B&W (IR-CUT)
Image Config	Saturation/Brightness/Contrast /Sharpness, Mirror, 3D NR , White Balance, FLK(Flicker Control)
Corridor Pattern	N/A
Defog Mode	N/A
BLC	Supported
WDR	Supported
Motion Detection	Supported
Privacy Masking	3 Rectangular Zone
Recording Mode	NVR/NAS/CMS/Web
Language	Chinese Simplified, Chinese Traditional, English, Bulgarian, Polish, Farsi, German, Russian, French, Korean, Portuguese, Japanese, Turkish, Spanish, Hebrew, Italian,Nederlands
General	
Housing	Metal, IP66
Anti-cut Bracket	3-Axis
IR Cut Filter	YES
Operation Temperature	S
Storage Temperature	-20 ~ +60 RH95% Max
Power Source	DC12V±10%, 500mA
Dimension	157(W) x 70(H) x 66(D)mm
Weight	650g

019730