

## Digital Wireless Observation Set 2.4 Ghz - 1x Camera

### General information

Wireless observation set to enable remote surveillance while you are away from home. The 4-channel recorder with integrated 7" colour LCD monitor is supplied with an RJ45 dongle to connect it with an existing network which supports mobile viewing via a free app. The camera is water-resistant (IP54) and features night vision (up to 5 metres) and motion detection. Videos are either stored on SD (max. 32 Gb) or USB (max. 1 Tb), both not included.

### Features

- Free mobile app to enable remote surveillance
- Easy 3-step installation: unpack, plug in and power up!
- Weatherproof camera, featuring IP54 protection
- Night vision up to 5 metres
- Reliable 2.4 GHz digital wireless technology

### Specifications

Lens:	2.00 mm
Image chip:	CMOS
Viewing angle:	73 °
Operating temperature:	-10 - 50 °C
Night vision:	5.00 m
LED:	9
No. of cameras:	1x Camera
Accessories:	Camera Mount
Accessories:	Network Dongle
Accessories:	AV Cable
Max. resolution:	VGA
Input voltage:	220 - 240 VAC
Camera design:	Bullet
Screen size:	7 "
Type:	Set
Camera input:	4
IP rating:	IP54



### Sales information

Order code:	<b>SAS-TRANS62U</b>
Product description:	Digital Wireless Observation Set 2.4 Ghz - 1x Camera
Packaging:	Giftbox
Brand name:	König



Quantity	LxWxH (mm)	Weight
1	275x95x365	1771 gr.
8	400x390x555	15080 gr.



## Digital Wireless Observation Set 2.4 Ghz - 1x Camera

Features:	App
Features:	1-Way Audio
Features:	Incl 1x Bullet
Features:	Motion Sensor
Wireless technology:	2.4 Ghz
Power plug:	UK / Type G
Interface:	AV
Interface:	LAN
Storage type:	SD
Storage type:	USB

### Package contents

1x LCD monitor 4ch incl. PSU UK  
1x wireless camera incl. PSU UK  
1x camera bracket incl. installation materials  
1x RJ45 dongle  
manual