



connecting the future

TRIAx



LTE WFAV 25 - 1 Input - Wideband Masthead Amplifier & Power Supply Kit

Article number: 370559

Product description:

Wolsey LTE Masthead Amplifier Kit

- F-Connector Masthead Amplifier and Power Supply Kit
- 1 Input 1 Output
- 10-25 dB Variable Gain
- Weatherproof housing
- Fully screened enclosure

Specifications

ORDER INFORMATION	
EAN Number	5702663705593
CHARACTERISTICS	
Max. Output level @ 60 dB IMD	102 dB μ V
Type	Wideband mast amplifier
FREQUENCY	
Input 1 - band	UHF (T)
Input 1 - channels	21...60
Input 1 - frequency	470...790 MHz
LTE protection	800
GAIN	
Input 1 - gain	10-25 dB
Input 1 - noise figure	<2.2 dB
RETURN LOSS	
Return Loss	10 Typ dB
ELECTRICAL	
Impedance	75 Ω
OPERATIONAL	
DC Operating voltage	12 VDC
DC Current consumption	100 mA
CONNECTORS	
Connector Type	F-female
Number of inputs	1
Number of outputs	1
MECHANICAL	
Colour	Black
Product Depth	60 mm
Total Weight	0,590 kg
Net Weight	0,525 kg
Remarks	Kit includes WPS 100 Power Supply, 12VDC, 100mA Max Fully screened
Tara Weight	0,065 kg

Packaging Volume	0,001 m3
Product Width	120 mm
Product Height	215 mm
