

## Basic

Bluetooth:	No
Brand Name:	Lenovo
Colour:	Black
DisplayPort:	Yes
Energy Star:	Yes
Environmentally Friendly:	Yes
Form Factor:	Small Form Factor
Graphics Controller	Intel
Manufacturer:	
Graphics Controller Model:	HD Graphics 630
Graphics Memory Accessibility:	Shared
Graphics Memory Technology:	DDR4 SDRAM
HDMI:	Yes
Monitor Included:	No
Number of DisplayPort Outputs:	1
Number of USB 2.0 Ports:	2
Number of USB 3.0 Ports:	6
Operating System Architecture:	64-bit
Operating System Platform:	Windows
Operating System:	Windows 10 Pro
Optical Drive Type:	DVD-Writer
Processor Manufacturer:	Intel
Processor Model:	i5-7400
Processor Speed:	3 GHz
Processor Type:	Core i5
Product Family:	V520S-08IKL
Product Type:	Desktop Computer
Standard Memory:	4 GB
Total Hard Drive Capacity:	500 GB
Total Number of USB Ports:	8
VGA:	Yes
Wireless LAN:	No

## Display & Graphics

Graphics Controller	Intel
Manufacturer:	
Graphics Controller Model:	HD Graphics 630
Graphics Memory Accessibility:	Shared
Graphics Memory Technology:	DDR4 SDRAM
Monitor Included:	No

## General Information

Brand Name:	Lenovo
Manufacturer Part Number:	10NM0025UK
Manufacturer Website Address:	<a href="http://www.lenovo.com/uk/en/">http://www.lenovo.com/uk/en/</a>
Manufacturer:	Lenovo Group Limited
Product Model:	10NM0025UK
Product Name:	V520S-08IKL 10NM0025UK Desktop Computer
Product Series:	V520S-08IKL
Product Type:	Desktop Computer

## Interfaces/Ports

DisplayPort:	Yes
HDMI:	Yes
Number of DisplayPort Outputs:	1
Number of USB 2.0 Ports:	2
Number of USB 3.0 Ports:	6
Total Number of USB Ports:	8
VGA:	Yes

## Memory

Memory Technology:	DDR4 SDRAM
Standard Memory:	4 GB

## Miscellaneous

Energy Star:	Yes
Environmental Certification:	ENERGY STAR 6.1 ErP Lot 3 GREENGUARD RoHS
Environmentally Friendly:	Yes
Features:	Security Slot
Package Contents:	

- V520S-08IKL 10NM0025UK Desktop Computer
- Keyboard
- Mouse

### **Network & Communication**

Bluetooth: No  
Wireless LAN: No

### **Physical Characteristics**

Colour: Black  
Depth: 345.4 mm  
Form Factor: Small Form Factor  
Height: 88.9 mm  
Weight (Approximate): 4.76 kg  
Width: 289.6 mm

### **Processor & Chipset**

Processor Generation: 7th Gen  
Processor Manufacturer: Intel  
Processor Model: i5-7400  
Processor Speed: 3 GHz  
Processor Type: Core i5

### **Software**

Operating System Architecture: 64-bit  
Operating System Platform: Windows  
Operating System: Windows 10 Pro

### **Storage**

Optical Drive Type: DVD-Writer  
Optical Media Supported: DVD±R/±RW  
Total Hard Drive Capacity: 500 GB

### **Warranty**

Limited Warranty: 1 Year