

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0466230501](#)
Status: **Active**
Overview: [Micro-Fit 3.0 Connector System Product Family](#)
Description: [Micro-Fit BMI™ Receptacle Housing, Single Row, Panel Mount, 5 Circuits, Nylon, UL 94V-0](#)

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Packaging Specification 466230000-PK-000 \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

CSA LR19980
 UL E29179

General

Product Family [Crimp Housings](#)
 Series [46623](#)
 Application [Power, Wire-to-Board, Wire-to-Wire](#)
 Overview [Micro-Fit 3.0 Connector System Product Family](#)
 Product Literature Order No 987650-5984
 Product Name [Micro-Fit BMI™](#)
 UPC 887191458687

Physical

Circuits (maximum) 5
 Color - Resin Black
 Flammability 94V-0
 Gender Receptacle
 Glow-Wire Compliant No
 Lock to Mating Part No
 Material - Resin Nylon
 Net Weight 1.478/g
 Number of Rows 1
 Packaging Type Bag
 Panel Mount Yes
 Pitch - Mating Interface 3.00mm
 Polarized to Mating Part Yes
 Stackable No
 Temperature Range - Operating -40°C to +105°C


Solder Process Data

Lead-freeProcess Capability N/A

Material Info

Reference - Drawing Numbers

Packaging Specification 466230000-PK-000
 Sales Drawing SD-46623-001-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 ED/30/2017 (7 July
 2017)

Halogen-Free

Status

Low-Halogen

**Need more information on product
 environmental compliance?**

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any
 non-product compliance questions.

China ROHS Green Image
 ELV Not Relevant
 RoHS Phthalates Not Contained

Search Parts in this Series

[46623](#) Series

Mates With

[46625](#) Micro-Fit BMI™ Plug Housing, [46622](#)
 Micro-Fit BMI™ Right Angle Header

Use With

[43030](#) , [45773](#) Micro-Fit 3.0™ Female Crimp
 Terminals, [46235](#) Micro-Fit RMF™ Female
 Crimp Terminals