



1MP IR Dome HD Camera

- . 1/4" 1.0MP CMOS Sensor
- . AHD/CVI/TVI/CVBS 4 IN 1
- . 3.6mm Fixed Lens
- . IR Distance max 20m
- . OSD&UTC support



SPECIFICATION

Model NO.	DFR11
Video Output Mode	AHD/CVI/TVI/CVBS 4 IN 1
Camera	
Image Sensor	1/4" 1.0MP CMOS Sensor
Image Resolution	1MP 720P/ 960H
Effective Pixels	1280*720
TV System	PAL/NTSC
Electronic Shutter	1/25s~1/50,000s , 1/30s~1/60,000s
S/N Ratio	≥50dB
Scanning System	Progressive Scan
Lens	
Focus Length	3.6mm
Focus Control	Fixed
Lens Type	Fixed
Pixels	2M Pixels
Auto Iris Support	NO

Night Vision

Infrared LED	14 μ x 18PCS
Infrared Distance	20M
IR Status	Under 10 Lux by CDS
IR Power On	CDS Auto Control

Camera Features

Starlight	/
Day/Night	YES
OSD Menu Language	YES
White Balance	AUTO / MANUAL
Gain Control	AUTO
Noise Reduction	DNR
Picture Adjustment	YES
WDR	YES
OSD Support	YES
UTC	YES
Dip Switch	Optional

General

Housing	Plastic
Bracket	NO
Dual Voltage	NO
IR Cut Filter	YES
Heater	NO
Audio	/
Operation Temperature	-10 $^{\circ}$ C ~ +50 $^{\circ}$ C RH95% Max
Storage Temperature	-20 $^{\circ}$ C ~ +60 $^{\circ}$ C RH95% Max
Power Source	DC12V \pm 10%, 550mA
Dimension	90.5(W) x 80(H) x 80(D)mm
Weight	300g