



2MP IR Bullet HD Camera

- . 1/2.7" 2MP CMOS Sensor
- . AHD/CVI/TVI/CVBS 4 IN 1
- . 2.8-12mm Varifocal Lens
- . IR Distance max 40m
- . IP66 outdoor, OSD&UTC support



SPECIFICATION	
Model NO.	DFR30
Video Output Mode	AHD/CVI/TVI/CVBS 4 IN 1
Camera	
Image Sensor	1/2.7" 2MP CMOS Sensor
Image Resolution	2MP 1080P/960H
Effective Pixels	1920*1080
TV System	PAL/NTSC
Electronic Shutter	1/25s~1/50,000s , 1/30s~1/60,000s
S/N Ratio	≥50dB
Scanning System	Progressive Scan
Lens	
Focus Length	2.8-12mm
Focus Control	Manual
Lens Type	Varifocal
Pixels	2M Pixels
Auto Iris Support	NO

Night Vision	
Infrared LED	42μ x 4PCS
Infrared Distance	40M
IR Status	Under 10 Lux by CDS
IR Power On	CDS Auto Control
Camera Features	
Starlight	/
Day/Night	YES
OSD Menu Language	YES
White Balance	AUTO / MANUAL
Gain Control	AUTO
Noise Reduction	DNR
Picture Adjustment	YES
WDR	YES
OSD Support	YES
UTC	YES
Dip Switch	Optional
General	
Housing	Metal, IP66
Bracket	YES
Dual Voltage	Optional
IR Cut Filter	YES
Heater	Optional
Audio	/
Operation Temperature	-10°C ~ +50°C RH95% Max
Storage Temperature	-20°C ~ +60°C RH95% Max
Power Source	DC12V±10%, 700mA
Dimension	200(W) x 171(H) x 83(D)mm
Weight	1400g